

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580525

Luminaire Tested: **HCC4S35D010SL-HM43040940-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010SL-HM43040940-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2723.4 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580525
CATALOG NUMBER: HCC4S35D010SL-HM43040940-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P580525

CATALOG NUMBER: HCC4S35D010SL-HM43040940-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	271595
5°	271852
10°	272378
15°	276349
20°	269467
25°	252827
30°	223625
35°	170047
40°	107140
45°	61507
50°	32641
55°	13526
60°	3626
65°	3065
70°	2272
75°	2002
80°	1492
85°	2972



TEST NUMBER: P580525
 CATALOG NUMBER: HCC4S35D010SL-HM43040940-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.8	7.7
10°-20°	606.0	22.3
20°-30°	845.7	31.1
30°-40°	695.9	25.6
40°-50°	286.7	10.5
50°-60°	64.6	2.4
60°-70°	10.4	0.4
70°-80°	3.9	0.1
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.5	61.0
0°-40°	2356.5	86.5
0°-60°	2707.7	99.4
0°-90°	2723.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2723.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2202	
5°	2196	209
15°	2164	606
25°	1858	846
35°	1129	696
45°	353	287
55°	63	65
65°	10	10
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P580525
CATALOG NUMBER: HCC4S35D010SL-HM43040940-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2201.9
2.5°	2191.5
5°	2195.6
7.5°	2187.3
10°	2174.7
12.5°	2168.4
15°	2164.1
17.5°	2126.4
20°	2052.9
22.5°	1960.6
25°	1857.7
27.5°	1733.9
30°	1570.1
32.5°	1368.6
35°	1129.3
37.5°	888.0
40°	665.4
42.5°	484.9
45°	352.6
47.5°	251.9
50°	170.1
52.5°	107.0
55°	62.9
57.5°	31.5
60°	14.7
62.5°	12.6
65°	10.5
67.5°	8.4
70°	6.3
72.5°	4.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)