

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580527

Luminaire Tested: **HCC4W35D010SL-HM43040940-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010SL-HM43040940-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3086.6 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580527
CATALOG NUMBER: HCC4W35D010SL-HM43040940-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P580527
 CATALOG NUMBER: HCC4W35D010SL-HM43040940-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76		82	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65		73	68	64		71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60		68	63	60		67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56		64	59	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	399590
5°	391249
10°	369733
15°	345318
20°	315829
25°	282033
30°	236828
35°	166614
40°	102777
45°	61524
50°	36248
55°	18064
60°	9325
65°	6129
70°	3787
75°	3002
80°	1492
85°	2972



TEST NUMBER: P580527
 CATALOG NUMBER: HCC4W35D010SL-HM43040940-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.1	9.6
10°-20°	755.9	24.5
20°-30°	942.7	30.5
30°-40°	694.4	22.5
40°-50°	285.6	9.3
50°-60°	83.4	2.7
60°-70°	21.5	0.7
70°-80°	6.6	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1993.7	64.6
0°-40°	2688.1	87.1
0°-60°	3057.1	99.0
0°-90°	3086.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3086.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3240	
5°	3160	295
15°	2704	756
25°	2072	943
35°	1106	694
45°	353	286
55°	84	83
65°	21	21
75°	6	7
85°	2	1
90°	0	



TEST NUMBER: P580527
CATALOG NUMBER: HCC4W35D010SL-HM43040940-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3239.6
2.5°	3206.1
5°	3159.9
7.5°	3075.8
10°	2952.0
12.5°	2830.2
15°	2704.2
17.5°	2563.6
20°	2406.1
22.5°	2242.4
25°	2072.3
27.5°	1883.3
30°	1662.8
32.5°	1396.2
35°	1106.5
37.5°	850.3
40°	638.3
42.5°	472.4
45°	352.7
47.5°	260.3
50°	188.9
52.5°	130.2
55°	84.0
57.5°	50.4
60°	37.8
62.5°	27.3
65°	21.0
67.5°	14.7
70°	10.5
72.5°	8.4
75°	6.3
77.5°	4.2
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)