

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580536

Luminaire Tested: **HCC4S35D010MB-HM43040940-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S35D010MB-HM43040940-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2969.1 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580536
CATALOG NUMBER: HCC4S35D010MB-HM43040940-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580536

CATALOG NUMBER: HCC4S35D010MB-HM43040940-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257903
5°	256276
10°	250823
15°	245280
20°	233935
25°	216557
30°	188360
35°	142235
40°	103083
45°	80572
50°	68889
55°	59589
60°	54913
65°	50229
70°	46955
75°	43034
80°	40204
85°	38636



TEST NUMBER: P580536
 CATALOG NUMBER: HCC4S35D010MB-HM43040940-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	6.6
10°-20°	538.0	18.1
20°-30°	723.5	24.4
30°-40°	594.9	20.0
40°-50°	365.3	12.3
50°-60°	252.9	8.5
60°-70°	172.4	5.8
70°-80°	96.0	3.2
80°-90°	30.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1457.0	49.1
0°-40°	2051.9	69.1
0°-60°	2670.1	89.9
0°-90°	2969.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2969.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2091	
5°	2070	195
15°	1921	538
25°	1591	723
35°	945	595
45°	462	365
55°	277	253
65°	172	172
75°	90	96
85°	27	31
90°	0	



TEST NUMBER: P580536
CATALOG NUMBER: HCC4S35D010MB-HM43040940-41PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2090.9
2.5°	2076.1
5°	2069.8
7.5°	2046.7
10°	2002.6
12.5°	1962.7
15°	1920.8
17.5°	1859.9
20°	1782.2
22.5°	1689.8
25°	1591.2
27.5°	1471.5
30°	1322.5
32.5°	1139.8
35°	944.6
37.5°	776.7
40°	640.2
42.5°	535.2
45°	461.9
47.5°	405.2
50°	359.0
52.5°	317.0
55°	277.1
57.5°	247.7
60°	222.6
62.5°	197.4
65°	172.1
67.5°	151.2
70°	130.2
72.5°	109.1
75°	90.3
77.5°	71.4
80°	56.6
82.5°	42.0
85°	27.3
87.5°	14.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)