

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580535

Luminaire Tested: **HCC4W35D010MB-HM43040940-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010MB-HM43040940-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2889.3 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580535
CATALOG NUMBER: HCC4W35D010MB-HM43040940-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P580535
 CATALOG NUMBER: HCC4W35D010MB-HM43040940-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58		
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52		
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253833
5°	251955
10°	245387
15°	238921
20°	228225
25°	212638
30°	187221
35°	147671
40°	107172
45°	78758
50°	64073
55°	53740
60°	48697
65°	44742
70°	41654
75°	38030
80°	34308
85°	29720



TEST NUMBER: P580535
 CATALOG NUMBER: HCC4W35D010MB-HM43040940-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	6.6
10°-20°	524.8	18.2
20°-30°	711.4	24.6
30°-40°	610.5	21.1
40°-50°	360.5	12.5
50°-60°	228.4	7.9
60°-70°	153.5	5.3
70°-80°	84.7	2.9
80°-90°	23.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.1	49.4
0°-40°	2038.5	70.6
0°-60°	2627.4	90.9
0°-90°	2889.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2889.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2058	
5°	2035	192
15°	1871	525
25°	1562	711
35°	981	610
45°	452	360
55°	250	228
65°	153	153
75°	80	85
85°	21	24
90°	0	



TEST NUMBER: P580535
CATALOG NUMBER: HCC4W35D010MB-HM43040940-41NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2057.9
2.5°	2043.2
5°	2034.9
7.5°	2007.6
10°	1959.2
12.5°	1917.2
15°	1871.0
17.5°	1812.2
20°	1738.7
22.5°	1656.9
25°	1562.4
27.5°	1451.1
30°	1314.5
32.5°	1152.9
35°	980.7
37.5°	814.8
40°	665.6
42.5°	541.8
45°	451.5
47.5°	386.4
50°	333.9
52.5°	289.8
55°	249.9
57.5°	218.4
60°	197.4
62.5°	176.4
65°	153.3
67.5°	134.4
70°	115.5
72.5°	96.6
75°	79.8
77.5°	62.9
80°	48.3
82.5°	33.6
85°	21.0
87.5°	8.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)