

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580526

Luminaire Tested: **HCC4W35D010MB-HM43040940-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W35D010MB-HM43040940-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3389.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580526
CATALOG NUMBER: HCC4W35D010MB-HM43040940-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580526
 CATALOG NUMBER: HCC4W35D010MB-HM43040940-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278218
5°	279554
10°	281458
15°	284279
20°	279535
25°	266682
30°	242297
35°	195449
40°	135608
45°	89033
50°	59640
55°	42450
60°	36264
65°	41707
70°	44683
75°	43034
80°	38783
85°	35664



TEST NUMBER: P580526
 CATALOG NUMBER: HCC4W35D010MB-HM43040940-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.2	6.3
10°-20°	625.4	18.5
20°-30°	893.5	26.4
30°-40°	798.2	23.6
40°-50°	409.4	12.1
50°-60°	186.1	5.5
60°-70°	138.8	4.1
70°-80°	94.4	2.8
80°-90°	28.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1734.1	51.2
0°-40°	2532.3	74.7
0°-60°	3127.8	92.3
0°-90°	3389.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3389.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2256	
5°	2258	215
15°	2226	625
25°	1960	894
35°	1298	798
45°	510	409
55°	197	186
65°	143	139
75°	90	94
85°	25	28
90°	0	



TEST NUMBER: P580526

CATALOG NUMBER: HCC4W35D010MB-HM43040940-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2255.6
2.5°	2247.2
5°	2257.8
7.5°	2257.8
10°	2247.2
12.5°	2236.8
15°	2226.2
17.5°	2194.7
20°	2129.6
22.5°	2049.8
25°	1959.5
27.5°	1846.1
30°	1701.2
32.5°	1516.4
35°	1298.0
37.5°	1064.8
40°	842.2
42.5°	657.4
45°	510.4
47.5°	399.0
50°	310.8
52.5°	243.7
55°	197.4
57.5°	165.9
60°	147.0
62.5°	142.9
65°	142.9
67.5°	138.6
70°	123.9
72.5°	107.1
75°	90.3
77.5°	71.4
80°	54.6
82.5°	39.9
85°	25.2
87.5°	10.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)