

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580547

Luminaire Tested: **HCC4S40D010SL-HM43040827-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040827-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4012.5 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580547
CATALOG NUMBER: HCC4S40D010SL-HM43040827-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P580547
 CATALOG NUMBER: HCC4S40D010SL-HM43040827-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63		
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53		
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	337363
5°	339889
10°	344145
15°	352788
20°	355378
25°	345210
30°	316516
35°	260438
40°	189838
45°	123205
50°	69465
55°	32988
60°	13025
65°	8085
70°	5446
75°	3574
80°	1776
85°	3538



TEST NUMBER: P580547
 CATALOG NUMBER: HCC4S40D010SL-HM43040827-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.1	6.5
10°-20°	778.9	19.4
20°-30°	1155.3	28.8
30°-40°	1067.0	26.6
40°-50°	557.1	13.9
50°-60°	152.7	3.8
60°-70°	29.4	0.7
70°-80°	8.3	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2196.3	54.7
0°-40°	3263.3	81.3
0°-60°	3973.2	99.0
0°-90°	4012.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4012.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2735	
5°	2745	262
15°	2763	779
25°	2536	1155
35°	1730	1067
45°	706	557
55°	153	153
65°	28	29
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P580547
CATALOG NUMBER: HCC4S40D010SL-HM43040827-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2735.1
2.5°	2727.5
5°	2745.1
7.5°	2752.7
10°	2747.7
12.5°	2752.7
15°	2762.7
17.5°	2752.7
20°	2707.4
22.5°	2634.6
25°	2536.5
27.5°	2403.2
30°	2222.3
32.5°	1993.5
35°	1729.6
37.5°	1453.0
40°	1179.0
42.5°	927.6
45°	706.3
47.5°	517.9
50°	362.0
52.5°	241.4
55°	153.4
57.5°	90.5
60°	52.8
62.5°	37.7
65°	27.7
67.5°	20.1
70°	15.1
72.5°	10.1
75°	7.5
77.5°	5.0
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)