

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580570

Luminaire Tested: **HCC4S40D010SL-HM43040830-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040830-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3925.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580570
CATALOG NUMBER: HCC4S40D010SL-HM43040830-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P580570

CATALOG NUMBER: HCC4S40D010SL-HM43040830-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332774
5°	331012
10°	324970
15°	318118
20°	304501
25°	283149
30°	250615
35°	197798
40°	148006
45°	113873
50°	92377
55°	76621
60°	67741
65°	62721
70°	57846
75°	53138
80°	48302
85°	38494



TEST NUMBER: P580570
 CATALOG NUMBER: HCC4S40D010SL-HM43040830-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.7	6.4
10°-20°	698.6	17.8
20°-30°	948.6	24.2
30°-40°	821.7	20.9
40°-50°	515.9	13.1
50°-60°	324.5	8.3
60°-70°	213.2	5.4
70°-80°	117.6	3.0
80°-90°	32.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1900.0	48.4
0°-40°	2721.7	69.3
0°-60°	3562.2	90.8
0°-90°	3925.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3925.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2698	
5°	2673	253
15°	2491	699
25°	2080	949
35°	1314	822
45°	653	516
55°	356	325
65°	215	213
75°	112	118
85°	27	32
90°	0	



TEST NUMBER: P580570
CATALOG NUMBER: HCC4S40D010SL-HM43040830-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2697.9
2.5°	2681.5
5°	2673.4
7.5°	2646.2
10°	2594.6
12.5°	2542.9
15°	2491.2
17.5°	2420.5
20°	2319.8
22.5°	2205.6
25°	2080.5
27.5°	1936.4
30°	1759.6
32.5°	1544.7
35°	1313.6
37.5°	1101.5
40°	919.2
42.5°	775.1
45°	652.8
47.5°	560.3
50°	481.4
52.5°	413.4
55°	356.3
57.5°	307.3
60°	274.6
62.5°	244.7
65°	214.9
67.5°	185.0
70°	160.4
72.5°	133.3
75°	111.5
77.5°	87.0
80°	68.0
82.5°	46.2
85°	27.2
87.5°	10.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)