

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580562

Luminaire Tested: **HCC4W40D010BZ-HM43040830-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010BZ-HM43040830-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4387.3 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580562
CATALOG NUMBER: HCC4W40D010BZ-HM43040830-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580562
 CATALOG NUMBER: HCC4W40D010BZ-HM43040830-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360169
5°	361892
10°	364360
15°	368022
20°	361875
25°	345237
30°	313653
35°	253015
40°	175556
45°	115251
50°	77217
55°	54966
60°	46945
65°	53965
70°	57846
75°	55711
80°	50220
85°	46137



TEST NUMBER: P580562
 CATALOG NUMBER: HCC4W40D010BZ-HM43040830-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.5	6.3
10°-20°	809.6	18.5
20°-30°	1156.7	26.4
30°-40°	1033.3	23.6
40°-50°	530.0	12.1
50°-60°	240.9	5.5
60°-70°	179.7	4.1
70°-80°	122.3	2.8
80°-90°	36.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2244.9	51.2
0°-40°	3278.2	74.7
0°-60°	4049.1	92.3
0°-90°	4387.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4387.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2920	
5°	2923	279
15°	2882	810
25°	2537	1157
35°	1680	1033
45°	661	530
55°	256	241
65°	185	180
75°	117	122
85°	33	36
90°	0	



TEST NUMBER: P580562
CATALOG NUMBER: HCC4W40D010BZ-HM43040830-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2920.0
2.5°	2909.1
5°	2922.8
7.5°	2922.8
10°	2909.1
12.5°	2895.5
15°	2882.0
17.5°	2841.2
20°	2756.9
22.5°	2653.6
25°	2536.7
27.5°	2389.9
30°	2202.2
32.5°	1963.0
35°	1680.3
37.5°	1378.5
40°	1090.3
42.5°	851.0
45°	660.7
47.5°	516.6
50°	402.4
52.5°	315.3
55°	255.6
57.5°	214.8
60°	190.3
62.5°	184.9
65°	184.9
67.5°	179.5
70°	160.4
72.5°	138.7
75°	116.9
77.5°	92.5
80°	70.7
82.5°	51.7
85°	32.6
87.5°	13.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)