

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580608

Luminaire Tested: **HCC4S40D010SL-HM43040840-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040840-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4033.1 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580608
CATALOG NUMBER: HCC4S40D010SL-HM43040840-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580608
 CATALOG NUMBER: HCC4S40D010SL-HM43040840-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84		89	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	84	78	74		81	77	73		79	75	72	70
4	90	80	73	68	88	79	72	67	77	71	66		74	69	65		72	68	65	63
5	84	74	66	61	82	72	66	60	71	64	60		69	63	59		67	62	59	57
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62	57	53	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	65	54	47	42	53	47	42		52	46	42		51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350314
5°	348123
10°	340713
15°	333174
20°	317771
25°	294160
30°	255856
35°	193221
40°	140036
45°	109424
50°	93566
55°	80944
60°	74550
65°	68237
70°	63761
75°	58428
80°	54695
85°	52505



TEST NUMBER: P580608
 CATALOG NUMBER: HCC4S40D010SL-HM43040840-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.5	6.6
10°-20°	730.8	18.1
20°-30°	982.8	24.4
30°-40°	808.1	20.0
40°-50°	496.2	12.3
50°-60°	343.4	8.5
60°-70°	234.1	5.8
70°-80°	130.5	3.2
80°-90°	41.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1979.1	49.1
0°-40°	2787.2	69.1
0°-60°	3626.9	89.9
0°-90°	4033.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4033.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2840	
5°	2812	266
15°	2609	731
25°	2161	983
35°	1283	808
45°	627	496
55°	376	343
65°	234	234
75°	123	130
85°	37	42
90°	0	



TEST NUMBER: P580608
CATALOG NUMBER: HCC4S40D010SL-HM43040840-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2840.1
2.5°	2820.1
5°	2811.6
7.5°	2780.2
10°	2720.3
12.5°	2666.1
15°	2609.1
17.5°	2526.4
20°	2420.9
22.5°	2295.5
25°	2161.4
27.5°	1998.9
30°	1796.4
32.5°	1548.3
35°	1283.2
37.5°	1055.1
40°	869.7
42.5°	727.1
45°	627.3
47.5°	550.3
50°	487.6
52.5°	430.6
55°	376.4
57.5°	336.5
60°	302.2
62.5°	268.0
65°	233.8
67.5°	205.3
70°	176.8
72.5°	148.3
75°	122.6
77.5°	97.0
80°	77.0
82.5°	57.1
85°	37.1
87.5°	20.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)