

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580618

Luminaire Tested: **HCC4W40D010SL-HM43040927-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010SL-HM43040927-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3013.5 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580618
CATALOG NUMBER: HCC4W40D010SL-HM43040927-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580618
 CATALOG NUMBER: HCC4W40D010SL-HM43040927-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63		
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54		
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390858
5°	383745
10°	363997
15°	340350
20°	309108
25°	273527
30°	227513
35°	164069
40°	102390
45°	59047
50°	33312
55°	15870
60°	9103
65°	6975
70°	4688
75°	3098
80°	3125
85°	2972



TEST NUMBER: P580618
 CATALOG NUMBER: HCC4W40D010SL-HM43040927-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.7	9.6
10°-20°	743.5	24.7
20°-30°	914.4	30.3
30°-40°	679.1	22.5
40°-50°	276.0	9.2
50°-60°	76.5	2.5
60°-70°	23.8	0.8
70°-80°	8.0	0.3
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1947.7	64.6
0°-40°	2626.8	87.2
0°-60°	2979.3	98.9
0°-90°	3013.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3013.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3169	
5°	3099	290
15°	2665	744
25°	2010	914
35°	1090	679
45°	338	276
55°	74	76
65°	24	24
75°	6	8
85°	2	2
90°	0	



TEST NUMBER: P580618
CATALOG NUMBER: HCC4W40D010SL-HM43040927-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3168.8
2.5°	3138.5
5°	3099.3
7.5°	3021.2
10°	2906.2
12.5°	2786.8
15°	2665.3
17.5°	2519.9
20°	2354.9
22.5°	2187.7
25°	2009.8
27.5°	1816.7
30°	1597.4
32.5°	1347.9
35°	1089.6
37.5°	846.5
40°	635.9
42.5°	464.4
45°	338.5
47.5°	243.0
50°	173.6
52.5°	119.4
55°	73.8
57.5°	47.8
60°	36.9
62.5°	30.4
65°	23.9
67.5°	17.4
70°	13.0
72.5°	10.9
75°	6.5
77.5°	4.4
80°	4.4
82.5°	2.1
85°	2.1
87.5°	2.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)