

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580623

Luminaire Tested: **HCC4W40D010SL-HM43040927-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010SL-HM43040927-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3684.4 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580623
CATALOG NUMBER: HCC4W40D010SL-HM43040927-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P580623

CATALOG NUMBER: HCC4W40D010SL-HM43040927-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77				
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71				
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65				
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60				
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51				
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47				
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297645
5°	302002
10°	311480
15°	332816
20°	352661
25°	348803
30°	313069
35°	243664
40°	165074
45°	103057
50°	44596
55°	14946
60°	3750
65°	2539
70°	1587
75°	1001
80°	1492
85°	0



TEST NUMBER: P580623
 CATALOG NUMBER: HCC4W40D010SL-HM43040927-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.3	6.4
10°-20°	739.9	20.1
20°-30°	1159.3	31.5
30°-40°	1000.5	27.2
40°-50°	460.1	12.5
50°-60°	78.1	2.1
60°-70°	8.8	0.2
70°-80°	3.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2133.4	57.9
0°-40°	3133.9	85.1
0°-60°	3672.2	99.7
0°-90°	3684.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3684.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2413	
5°	2439	234
15°	2606	740
25°	2563	1159
35°	1618	1001
45°	591	460
55°	70	78
65°	9	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580623
CATALOG NUMBER: HCC4W40D010SL-HM43040927-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2413.1
2.5°	2413.1
5°	2439.1
7.5°	2463.1
10°	2486.9
12.5°	2536.8
15°	2606.3
17.5°	2665.0
20°	2686.7
22.5°	2654.2
25°	2562.9
27.5°	2415.2
30°	2198.1
32.5°	1924.3
35°	1618.2
37.5°	1309.7
40°	1025.2
42.5°	784.0
45°	590.8
47.5°	414.9
50°	232.4
52.5°	128.1
55°	69.5
57.5°	34.8
60°	15.2
62.5°	10.9
65°	8.7
67.5°	6.5
70°	4.4
72.5°	4.4
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)