

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580616

Luminaire Tested: **HCC4S40D010SL-HM43040927-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040927-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3504.2 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580616
CATALOG NUMBER: HCC4S40D010SL-HM43040927-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580616
 CATALOG NUMBER: HCC4S40D010SL-HM43040927-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	287691
5°	289050
10°	291027
15°	293945
20°	289038
25°	275746
30°	250530
35°	202090
40°	140213
45°	92050
50°	61674
55°	43891
60°	37497
65°	43079
70°	46198
75°	44512
80°	40133
85°	36796



TEST NUMBER: P580616
 CATALOG NUMBER: HCC4S40D010SL-HM43040927-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.5	6.3
10°-20°	646.7	18.5
20°-30°	923.9	26.4
30°-40°	825.3	23.6
40°-50°	423.3	12.1
50°-60°	192.4	5.5
60°-70°	143.5	4.1
70°-80°	97.7	2.8
80°-90°	29.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1793.0	51.2
0°-40°	2618.4	74.7
0°-60°	3234.1	92.3
0°-90°	3504.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3504.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2332	
5°	2334	222
15°	2302	647
25°	2026	924
35°	1342	825
45°	528	423
55°	204	192
65°	148	143
75°	93	98
85°	26	29
90°	0	



TEST NUMBER: P580616
CATALOG NUMBER: HCC4S40D010SL-HM43040927-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2332.4
2.5°	2323.6
5°	2334.5
7.5°	2334.5
10°	2323.6
12.5°	2312.7
15°	2301.9
17.5°	2269.4
20°	2202.0
22.5°	2119.5
25°	2026.1
27.5°	1908.8
30°	1759.0
32.5°	1567.9
35°	1342.1
37.5°	1101.0
40°	870.8
42.5°	679.7
45°	527.7
47.5°	412.6
50°	321.4
52.5°	251.9
55°	204.1
57.5°	171.5
60°	152.0
62.5°	147.6
65°	147.6
67.5°	143.4
70°	128.1
72.5°	110.8
75°	93.4
77.5°	73.9
80°	56.5
82.5°	41.3
85°	26.0
87.5°	10.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)