

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580641

Luminaire Tested: **HCC4W40D010MB-HM43040930-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580641  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W40D010MB-HM43040930-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3954.4 lumens  
Efficiency: N/A  
Efficacy: 96.4 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580641  
CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P580641

CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	319441
5°	324128
10°	334301
15°	357193
20°	378493
25°	374348
30°	335986
35°	261507
40°	177166
45°	110593
50°	47858
55°	16021
60°	4046
65°	2714
70°	1695
75°	1144
80°	1705
85°	0



TEST NUMBER: P580641  
 CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	251.5	6.4
10°-20°	794.1	20.1
20°-30°	1244.2	31.5
30°-40°	1073.8	27.2
40°-50°	493.8	12.5
50°-60°	83.8	2.1
60°-70°	9.5	0.2
70°-80°	3.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2289.7	57.9
0°-40°	3363.5	85.1
0°-60°	3941.1	99.7
0°-90°	3954.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3954.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2590	
5°	2618	251
15°	2797	794
25°	2751	1244
35°	1737	1074
45°	634	494
55°	74	84
65°	9	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580641  
CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2589.8
2.5°	2589.8
5°	2617.8
7.5°	2643.4
10°	2669.1
12.5°	2722.7
15°	2797.2
17.5°	2860.2
20°	2883.5
22.5°	2848.6
25°	2750.6
27.5°	2592.1
30°	2359.0
32.5°	2065.3
35°	1736.7
37.5°	1405.6
40°	1100.3
42.5°	841.5
45°	634.0
47.5°	445.3
50°	249.4
52.5°	137.5
55°	74.5
57.5°	37.3
60°	16.4
62.5°	11.7
65°	9.3
67.5°	7.0
70°	4.7
72.5°	4.7
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)