

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580644

Luminaire Tested: **HCC4S40D010MW-HM43040930-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010MW-HM43040930-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3294.9 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580644
CATALOG NUMBER: HCC4S40D010MW-HM43040930-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580644
 CATALOG NUMBER: HCC4S40D010MW-HM43040930-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286187
5°	284395
10°	278352
15°	272198
20°	259609
25°	240320
30°	209026
35°	157835
40°	114402
45°	89399
50°	76450
55°	66127
60°	60933
65°	55745
70°	52076
75°	47752
80°	44679
85°	42882



TEST NUMBER: P580644
 CATALOG NUMBER: HCC4S40D010MW-HM43040930-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.9	6.6
10°-20°	597.1	18.1
20°-30°	802.9	24.4
30°-40°	660.2	20.0
40°-50°	405.4	12.3
50°-60°	280.6	8.5
60°-70°	191.2	5.8
70°-80°	106.6	3.2
80°-90°	33.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1616.9	49.1
0°-40°	2277.0	69.1
0°-60°	2963.1	89.9
0°-90°	3294.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3294.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2320	
5°	2297	217
15°	2132	597
25°	1766	803
35°	1048	660
45°	512	405
55°	308	281
65°	191	191
75°	100	107
85°	30	34
90°	0	



TEST NUMBER: P580644
CATALOG NUMBER: HCC4S40D010MW-HM43040930-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2320.2
2.5°	2303.9
5°	2296.9
7.5°	2271.3
10°	2222.4
12.5°	2178.1
15°	2131.6
17.5°	2064.0
20°	1977.8
22.5°	1875.3
25°	1765.8
27.5°	1633.0
30°	1467.6
32.5°	1264.9
35°	1048.2
37.5°	861.9
40°	710.5
42.5°	594.0
45°	512.5
47.5°	449.6
50°	398.4
52.5°	351.8
55°	307.5
57.5°	274.9
60°	247.0
62.5°	218.9
65°	191.0
67.5°	167.7
70°	144.4
72.5°	121.2
75°	100.2
77.5°	79.3
80°	62.9
82.5°	46.6
85°	30.3
87.5°	16.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)