

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580645

Luminaire Tested: **HCC4W40D010MB-HM43040930-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MB-HM43040930-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3471.9 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580645
CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580645

CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39																			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	277565	277565	277565
5°	276891	277176	277176
10°	273680	273968	273680
15°	270398	270398	270398
20°	259294	259898	260213
25°	242538	242851	243477
30°	217316	217985	217985
35°	176446	177847	178178
40°	133160	133917	134271
45°	101993	101592	101592
50°	84049	83588	83588
55°	72127	71654	71654
60°	64362	63794	63794
65°	60503	60503	60503
70°	56260	56260	56260
75°	51088	52185	51088
80°	48018	46313	48018
85°	39485	39485	39485



TEST NUMBER: P580645
 CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.0	6.1
10°-20°	593.3	17.1
20°-30°	815.3	23.5
30°-40°	733.1	21.1
40°-50°	463.2	13.3
50°-60°	302.4	8.7
60°-70°	204.9	5.9
70°-80°	115.3	3.3
80°-90°	32.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1620.6	46.7
0°-40°	2353.7	67.8
0°-60°	3119.3	89.8
0°-90°	3471.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3471.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2250	2250	2250	2250	2250	
5°	2236	2236	2239	2239	2239	212
15°	2118	2118	2118	2118	2118	593
25°	1782	1784	1784	1789	1789	813
35°	1172	1176	1181	1186	1183	730
45°	585	582	582	582	582	464
55°	335	335	333	335	333	304
65°	207	207	207	207	207	205
75°	107	110	110	110	107	115
85°	28	28	28	28	28	33
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580645

CATALOG NUMBER: HCC4W40D010MB-HM43040930-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2250.3	2250.3	2250.3	2250.3	2250.3
2.5°	2238.6	2238.6	2238.6	2238.6	2238.6
5°	2236.3	2236.3	2238.6	2238.6	2238.6
7.5°	2220.0	2222.4	2222.4	2222.4	2222.4
10°	2185.1	2185.1	2187.4	2187.4	2185.1
12.5°	2152.4	2152.4	2152.4	2154.8	2152.4
15°	2117.5	2117.5	2117.5	2117.5	2117.5
17.5°	2056.9	2059.3	2059.3	2059.3	2059.3
20°	1975.4	1980.0	1980.0	1982.4	1982.4
22.5°	1882.3	1884.5	1886.9	1889.2	1886.9
25°	1782.1	1784.4	1784.4	1789.0	1789.0
27.5°	1665.6	1667.9	1672.5	1672.5	1672.5
30°	1525.8	1528.1	1530.5	1530.5	1530.5
32.5°	1360.4	1360.4	1365.0	1367.4	1365.0
35°	1171.8	1176.4	1181.1	1185.7	1183.3
37.5°	992.3	997.0	999.4	999.4	1001.7
40°	827.0	831.7	831.7	836.3	833.9
42.5°	696.5	694.2	694.2	698.8	696.5
45°	584.7	582.4	582.4	582.4	582.4
47.5°	503.2	500.9	500.9	500.9	500.9
50°	438.0	435.6	435.6	435.6	435.6
52.5°	384.4	382.0	382.0	382.0	379.7
55°	335.4	335.4	333.2	335.4	333.2
57.5°	291.2	291.2	291.2	291.2	291.2
60°	260.9	258.6	258.6	258.6	258.6
62.5°	232.9	232.9	232.9	232.9	232.9
65°	207.3	207.3	207.3	207.3	207.3
67.5°	181.7	179.4	181.7	181.7	179.4
70°	156.0	153.8	156.0	156.0	156.0
72.5°	130.5	130.5	130.5	132.7	130.5
75°	107.2	109.5	109.5	109.5	107.2
77.5°	86.2	88.6	86.2	86.2	86.2
80°	67.6	65.2	65.2	65.2	67.6
82.5°	46.6	46.6	46.6	46.6	46.6
85°	27.9	27.9	27.9	27.9	27.9
87.5°	11.7	11.7	11.7	11.7	11.7
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)