

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580662

Luminaire Tested: **HCC4S40D010SL-HM43040935-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040935-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3436.6 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580662
CATALOG NUMBER: HCC4S40D010SL-HM43040935-41PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P580662
 CATALOG NUMBER: HCC4S40D010SL-HM43040935-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298496
5°	296640
10°	290326
15°	283908
20°	270780
25°	250663
30°	218013
35°	164641
40°	119329
45°	93254
50°	79712
55°	68965
60°	63548
65°	58139
70°	54348
75°	49802
80°	46597
85°	44721



TEST NUMBER: P580662
 CATALOG NUMBER: HCC4S40D010SL-HM43040935-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.3	6.6
10°-20°	622.8	18.1
20°-30°	837.4	24.4
30°-40°	688.6	20.0
40°-50°	422.9	12.3
50°-60°	292.7	8.5
60°-70°	199.5	5.8
70°-80°	111.2	3.2
80°-90°	35.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1686.5	49.1
0°-40°	2375.0	69.1
0°-60°	3090.6	89.9
0°-90°	3436.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3436.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2420	
5°	2396	226
15°	2223	623
25°	1842	837
35°	1093	689
45°	535	423
55°	321	293
65°	199	199
75°	104	111
85°	32	35
90°	0	



TEST NUMBER: P580662
CATALOG NUMBER: HCC4S40D010SL-HM43040935-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2420.0
2.5°	2403.1
5°	2395.8
7.5°	2369.0
10°	2318.0
12.5°	2271.8
15°	2223.3
17.5°	2152.8
20°	2062.9
22.5°	1956.0
25°	1841.8
27.5°	1703.2
30°	1530.7
32.5°	1319.4
35°	1093.4
37.5°	899.0
40°	741.1
42.5°	619.6
45°	534.6
47.5°	468.9
50°	415.4
52.5°	366.9
55°	320.7
57.5°	286.8
60°	257.6
62.5°	228.3
65°	199.2
67.5°	175.0
70°	150.7
72.5°	126.3
75°	104.5
77.5°	82.6
80°	65.6
82.5°	48.7
85°	31.6
87.5°	17.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)