

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592818

Luminaire Tested: **HCC4W40D010MW-HM43040950-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MW-HM43040950-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3150.1 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592818
CATALOG NUMBER: HCC4W40D010MW-HM43040950-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P592818

CATALOG NUMBER: HCC4W40D010MW-HM43040950-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314149
5°	314445
10°	315037
15°	319651
20°	311681
25°	292431
30°	258662
35°	196684
40°	123934
45°	71153
50°	37726
55°	15677
60°	4194
65°	3532
70°	2633
75°	2288
80°	1776
85°	3538



TEST NUMBER: P592818
 CATALOG NUMBER: HCC4W40D010MW-HM43040950-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	7.7
10°-20°	700.9	22.3
20°-30°	978.2	31.1
30°-40°	805.0	25.6
40°-50°	331.6	10.5
50°-60°	74.7	2.4
60°-70°	12.0	0.4
70°-80°	4.5	0.1
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1920.6	61.0
0°-40°	2725.6	86.5
0°-60°	3131.9	99.4
0°-90°	3150.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3150.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2547	
5°	2540	242
15°	2503	701
25°	2149	978
35°	1306	805
45°	408	332
55°	73	75
65°	12	12
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P592818
CATALOG NUMBER: HCC4W40D010MW-HM43040950-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2546.9
2.5°	2534.7
5°	2539.6
7.5°	2529.9
10°	2515.3
12.5°	2508.0
15°	2503.2
17.5°	2459.5
20°	2374.5
22.5°	2267.7
25°	2148.7
27.5°	2005.5
30°	1816.1
32.5°	1583.0
35°	1306.2
37.5°	1027.1
40°	769.7
42.5°	560.8
45°	407.9
47.5°	291.3
50°	196.6
52.5°	123.9
55°	72.9
57.5°	36.4
60°	17.0
62.5°	14.6
65°	12.1
67.5°	9.8
70°	7.3
72.5°	4.8
75°	4.8
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)