

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580986

Luminaire Tested: **HCC4S05D010SL-HM40525827-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580986  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S05D010SL-HM40525827-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 564.5 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580986  
CATALOG NUMBER: HCC4S05D010SL-HM40525827-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580986

CATALOG NUMBER: HCC4S05D010SL-HM40525827-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49030
5°	48722
10°	47695
15°	46635
20°	44471
25°	41169
30°	35806
35°	27044
40°	19612
45°	15316
50°	13087
55°	11333
60°	10435
65°	9544
70°	8908
75°	8149
80°	7671
85°	7359



TEST NUMBER: P580986  
 CATALOG NUMBER: HCC4S05D010SL-HM40525827-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	6.6
10°-20°	102.3	18.1
20°-30°	137.6	24.4
30°-40°	113.1	20.0
40°-50°	69.5	12.3
50°-60°	48.1	8.5
60°-70°	32.8	5.8
70°-80°	18.3	3.2
80°-90°	5.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.0	49.1
0°-40°	390.1	69.1
0°-60°	507.7	89.9
0°-90°	564.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	398	
5°	394	37
15°	365	102
25°	302	138
35°	180	113
45°	88	69
55°	53	48
65°	33	33
75°	17	18
85°	5	6
90°	0	



TEST NUMBER: P580986  
CATALOG NUMBER: HCC4S05D010SL-HM40525827-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	397.5
2.5°	394.8
5°	393.5
7.5°	389.2
10°	380.8
12.5°	373.2
15°	365.2
17.5°	353.7
20°	338.8
22.5°	321.3
25°	302.5
27.5°	279.8
30°	251.4
32.5°	216.7
35°	179.6
37.5°	147.7
40°	121.8
42.5°	101.8
45°	87.8
47.5°	77.1
50°	68.2
52.5°	60.3
55°	52.7
57.5°	47.1
60°	42.3
62.5°	37.6
65°	32.7
67.5°	28.7
70°	24.7
72.5°	20.8
75°	17.1
77.5°	13.6
80°	10.8
82.5°	7.9
85°	5.2
87.5°	2.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)