

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580994

Luminaire Tested: **HCC4W05D010MB-HM40525830-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MB-HM40525830-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 697.9 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580994
CATALOG NUMBER: HCC4W05D010MB-HM40525830-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P580994
 CATALOG NUMBER: HCC4W05D010MB-HM40525830-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59				
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54				
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49				
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57306
5°	57562
10°	57952
15°	58536
20°	57571
25°	54915
30°	49907
35°	40249
40°	27920
45°	18333
50°	12281
55°	8731
60°	7475
65°	8581
70°	9196
75°	8864
80°	7956
85°	7359



TEST NUMBER: P580994
 CATALOG NUMBER: HCC4W05D010MB-HM40525830-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	6.3
10°-20°	128.8	18.5
20°-30°	184.0	26.4
30°-40°	164.4	23.6
40°-50°	84.3	12.1
50°-60°	38.3	5.5
60°-70°	28.6	4.1
70°-80°	19.4	2.8
80°-90°	5.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.1	51.2
0°-40°	521.5	74.7
0°-60°	644.1	92.3
0°-90°	697.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	697.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	465	
5°	465	44
15°	458	129
25°	404	184
35°	267	164
45°	105	84
55°	41	38
65°	29	29
75°	19	19
85°	5	6
90°	0	



TEST NUMBER: P580994

CATALOG NUMBER: HCC4W05D010MB-HM40525830-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	464.6
2.5°	462.7
5°	464.9
7.5°	464.9
10°	462.7
12.5°	460.6
15°	458.4
17.5°	452.0
20°	438.6
22.5°	422.1
25°	403.5
27.5°	380.1
30°	350.4
32.5°	312.2
35°	267.3
37.5°	219.3
40°	173.4
42.5°	135.4
45°	105.1
47.5°	82.2
50°	64.0
52.5°	50.2
55°	40.6
57.5°	34.2
60°	30.3
62.5°	29.4
65°	29.4
67.5°	28.5
70°	25.5
72.5°	22.0
75°	18.6
77.5°	14.8
80°	11.2
82.5°	8.2
85°	5.2
87.5°	2.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)