

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592531

Luminaire Tested: **HCC4W05D010MW-HM40525850-41WDWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592531  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010MW-HM40525850-41WDWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 743.4 lumens  
Efficiency: N/A  
Efficacy: 123.9 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592531  
CATALOG NUMBER: HCC4W05D010MW-HM40525850-41WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P592531  
 CATALOG NUMBER: HCC4W05D010MW-HM40525850-41WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	61019
5°	61314
10°	61735
15°	62354
20°	61325
25°	58494
30°	53154
35°	42869
40°	29756
45°	19520
50°	13087
55°	9333
60°	7943
65°	9135
70°	9773
75°	9484
80°	8524
85°	7925



TEST NUMBER: P592531  
 CATALOG NUMBER: HCC4W05D010MW-HM40525850-41WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.2	6.3
10°-20°	137.2	18.5
20°-30°	196.0	26.4
30°-40°	175.1	23.6
40°-50°	89.8	12.1
50°-60°	40.9	5.5
60°-70°	30.4	4.1
70°-80°	20.7	2.8
80°-90°	6.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.4	51.2
0°-40°	555.5	74.7
0°-60°	686.1	92.3
0°-90°	743.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	495	
5°	495	47
15°	488	137
25°	430	196
35°	285	175
45°	112	90
55°	43	41
65°	31	30
75°	20	21
85°	6	6
90°	0	



TEST NUMBER: P592531  
CATALOG NUMBER: HCC4W05D010MW-HM40525850-41WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	494.7
2.5°	492.9
5°	495.2
7.5°	495.2
10°	492.9
12.5°	490.7
15°	488.3
17.5°	481.5
20°	467.2
22.5°	449.6
25°	429.8
27.5°	405.0
30°	373.2
32.5°	332.7
35°	284.7
37.5°	233.6
40°	184.8
42.5°	144.1
45°	111.9
47.5°	87.5
50°	68.2
52.5°	53.5
55°	43.4
57.5°	36.4
60°	32.2
62.5°	31.3
65°	31.3
67.5°	30.4
70°	27.1
72.5°	23.5
75°	19.9
77.5°	15.7
80°	12.0
82.5°	8.7
85°	5.6
87.5°	2.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)