

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581054

Luminaire Tested: **HCC4W05D010BZ-HM40525927-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010BZ-HM40525927-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 505.4 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581054
CATALOG NUMBER: HCC4W05D010BZ-HM40525927-41NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581054

CATALOG NUMBER: HCC4W05D010BZ-HM40525927-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74451
5°	74352
10°	72907
15°	67807
20°	58293
25°	46831
30°	36561
35°	25598
40°	13139
45°	6663
50°	3339
55°	1247
60°	493
65°	409
70°	252
75°	143
80°	213
85°	0



TEST NUMBER: P581054
 CATALOG NUMBER: HCC4W05D010BZ-HM40525927-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	11.2
10°-20°	146.6	29.0
20°-30°	157.9	31.2
30°-40°	103.7	20.5
40°-50°	32.2	6.4
50°-60°	6.3	1.3
60°-70°	1.3	0.3
70°-80°	0.5	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.2	71.5
0°-40°	464.9	92.0
0°-60°	503.5	99.6
0°-90°	505.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	505.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	604	
5°	600	57
15°	531	147
25°	344	158
35°	170	104
45°	38	32
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P581054
CATALOG NUMBER: HCC4W05D010BZ-HM40525927-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	603.6
2.5°	600.5
5°	600.5
7.5°	595.8
10°	582.1
12.5°	560.2
15°	531.0
17.5°	491.7
20°	444.1
22.5°	392.9
25°	344.1
27.5°	298.7
30°	256.7
32.5°	217.1
35°	170.0
37.5°	118.5
40°	81.6
42.5°	56.3
45°	38.2
47.5°	26.0
50°	17.4
52.5°	10.9
55°	5.8
57.5°	2.4
60°	2.0
62.5°	1.7
65°	1.4
67.5°	1.0
70°	0.7
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)