

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581065

Luminaire Tested: **HCC4W05D010MB-HM40525930-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581065  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010MB-HM40525930-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 492.8 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581065  
CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581065  
 CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49153
5°	49205
10°	49285
15°	50019
20°	48764
25°	45756
30°	40478
35°	30778
40°	19386
45°	11129
50°	5910
55°	2452
60°	641
65°	555
70°	397
75°	381
80°	213
85°	425



TEST NUMBER: P581065  
 CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.8	7.7
10°-20°	109.7	22.3
20°-30°	153.1	31.1
30°-40°	126.0	25.6
40°-50°	51.9	10.5
50°-60°	11.7	2.4
60°-70°	1.9	0.4
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.5	61.0
0°-40°	426.5	86.5
0°-60°	490.0	99.4
0°-90°	492.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	398	
5°	397	38
15°	392	110
25°	336	153
35°	204	126
45°	64	52
55°	11	12
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581065  
CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	398.5
2.5°	396.6
5°	397.4
7.5°	395.9
10°	393.5
12.5°	392.4
15°	391.7
17.5°	384.8
20°	371.5
22.5°	354.8
25°	336.2
27.5°	313.8
30°	284.2
32.5°	247.7
35°	204.4
37.5°	160.7
40°	120.4
42.5°	87.7
45°	63.8
47.5°	45.6
50°	30.8
52.5°	19.4
55°	11.4
57.5°	5.7
60°	2.6
62.5°	2.3
65°	1.9
67.5°	1.5
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)