

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581067

Luminaire Tested: **HCC4S05D010MB-HM40525930-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010MB-HM40525930-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.5 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581067
CATALOG NUMBER: HCC4S05D010MB-HM40525930-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581067

CATALOG NUMBER: HCC4S05D010MB-HM40525930-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72305
5°	70798
10°	66908
15°	62495
20°	57151
25°	51036
30°	42856
35°	30146
40°	18597
45°	11129
50°	6563
55°	3269
60°	1678
65°	1080
70°	685
75°	524
80°	213
85°	425



TEST NUMBER: P581067
 CATALOG NUMBER: HCC4S05D010MB-HM40525930-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	9.6
10°-20°	136.8	24.5
20°-30°	170.6	30.5
30°-40°	125.7	22.5
40°-50°	51.7	9.3
50°-60°	15.1	2.7
60°-70°	3.9	0.7
70°-80°	1.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.8	64.6
0°-40°	486.5	87.1
0°-60°	553.2	99.1
0°-90°	558.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	586	
5°	572	53
15°	489	137
25°	375	171
35°	200	126
45°	64	52
55°	15	15
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581067
CATALOG NUMBER: HCC4S05D010MB-HM40525930-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	586.2
2.5°	580.2
5°	571.8
7.5°	556.6
10°	534.2
12.5°	512.2
15°	489.4
17.5°	464.0
20°	435.4
22.5°	405.8
25°	375.0
27.5°	340.8
30°	300.9
32.5°	252.7
35°	200.2
37.5°	153.9
40°	115.5
42.5°	85.5
45°	63.8
47.5°	47.1
50°	34.2
52.5°	23.6
55°	15.2
57.5°	9.1
60°	6.8
62.5°	5.0
65°	3.7
67.5°	2.6
70°	1.9
72.5°	1.5
75°	1.1
77.5°	0.8
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)