

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581077

Luminaire Tested: **HCC4W05D010MB-HM40525930-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MB-HM40525930-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 566.2 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581077
CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P581077
 CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	45256	45256	45256
5°	45156	45206	45206
10°	44639	44676	44639
15°	44094	44094	44094
20°	42279	42384	42424
25°	39550	39604	39713
30°	35436	35550	35550
35°	28775	29001	29061
40°	21705	21834	21898
45°	16624	16572	16572
50°	13701	13644	13644
55°	11763	11699	11699
60°	10509	10410	10410
65°	9865	9865	9865
70°	9160	9160	9160
75°	8340	8483	8340
80°	7814	7600	7814
85°	6369	6369	6369



TEST NUMBER: P581077
 CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.6	6.1
10°-20°	96.8	17.1
20°-30°	132.9	23.5
30°-40°	119.6	21.1
40°-50°	75.6	13.3
50°-60°	49.3	8.7
60°-70°	33.4	5.9
70°-80°	18.8	3.3
80°-90°	5.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.3	46.7
0°-40°	383.8	67.8
0°-60°	508.7	89.8
0°-90°	566.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	367	367	367	367	367	
5°	365	365	365	365	365	35
15°	345	345	345	345	345	97
25°	291	291	291	292	292	133
35°	191	192	193	193	193	119
45°	95	95	95	95	95	76
55°	55	55	54	55	54	49
65°	34	34	34	34	34	33
75°	18	18	18	18	18	19
85°	4	4	4	4	4	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581077

CATALOG NUMBER: HCC4W05D010MB-HM40525930-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	366.9	366.9	366.9	366.9	366.9
2.5°	365.1	365.1	365.1	365.1	365.1
5°	364.7	364.7	365.1	365.1	365.1
7.5°	362.1	362.4	362.4	362.4	362.4
10°	356.4	356.4	356.7	356.7	356.4
12.5°	351.1	351.1	351.1	351.4	351.1
15°	345.3	345.3	345.3	345.3	345.3
17.5°	335.4	335.8	335.8	335.8	335.8
20°	322.1	322.9	322.9	323.2	323.2
22.5°	306.9	307.4	307.7	308.0	307.7
25°	290.6	291.0	291.0	291.8	291.8
27.5°	271.6	271.9	272.7	272.7	272.7
30°	248.8	249.2	249.6	249.6	249.6
32.5°	221.9	221.9	222.6	223.0	222.6
35°	191.1	191.8	192.6	193.4	193.0
37.5°	161.9	162.6	163.0	163.0	163.3
40°	134.8	135.6	135.6	136.4	136.0
42.5°	113.6	113.2	113.2	114.0	113.6
45°	95.3	95.0	95.0	95.0	95.0
47.5°	82.1	81.7	81.7	81.7	81.7
50°	71.4	71.1	71.1	71.1	71.1
52.5°	62.7	62.3	62.3	62.3	62.0
55°	54.7	54.7	54.4	54.7	54.4
57.5°	47.4	47.4	47.4	47.4	47.4
60°	42.6	42.2	42.2	42.2	42.2
62.5°	38.0	38.0	38.0	38.0	38.0
65°	33.8	33.8	33.8	33.8	33.8
67.5°	29.6	29.3	29.6	29.6	29.3
70°	25.4	25.1	25.4	25.4	25.4
72.5°	21.2	21.2	21.2	21.7	21.2
75°	17.5	17.8	17.8	17.8	17.5
77.5°	14.1	14.4	14.1	14.1	14.1
80°	11.0	10.7	10.7	10.7	11.0
82.5°	7.6	7.6	7.6	7.6	7.6
85°	4.5	4.5	4.5	4.5	4.5
87.5°	1.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)