

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581094

Luminaire Tested: **HCC4S05D010BZ-HM40525935-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581094  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S05D010BZ-HM40525935-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 566.0 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581094  
CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581094

CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44		
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49166
5°	48846
10°	47820
15°	46763
20°	44590
25°	41292
30°	35906
35°	27119
40°	19644
45°	15368
50°	13125
55°	11354
60°	10460
65°	9573
70°	8980
75°	8245
80°	7671
85°	7359



TEST NUMBER: P581094  
 CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.3	6.6
10°-20°	102.6	18.1
20°-30°	137.9	24.4
30°-40°	113.4	20.0
40°-50°	69.6	12.3
50°-60°	48.2	8.5
60°-70°	32.9	5.8
70°-80°	18.3	3.2
80°-90°	5.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.8	49.1
0°-40°	391.2	69.1
0°-60°	509.0	89.9
0°-90°	566.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	399	
5°	394	37
15°	366	103
25°	303	138
35°	180	113
45°	88	70
55°	53	48
65°	33	33
75°	17	18
85°	5	6
90°	0	



TEST NUMBER: P581094

CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	398.6
2.5°	395.8
5°	394.5
7.5°	390.2
10°	381.8
12.5°	374.2
15°	366.2
17.5°	354.6
20°	339.7
22.5°	322.1
25°	303.4
27.5°	280.6
30°	252.1
32.5°	217.2
35°	180.1
37.5°	148.1
40°	122.0
42.5°	102.0
45°	88.1
47.5°	77.2
50°	68.4
52.5°	60.4
55°	52.8
57.5°	47.2
60°	42.4
62.5°	37.6
65°	32.8
67.5°	28.8
70°	24.9
72.5°	20.8
75°	17.3
77.5°	13.6
80°	10.8
82.5°	8.1
85°	5.2
87.5°	2.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)