

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592557

Luminaire Tested: **HCC4W05D010BZ-HM40525950-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010BZ-HM40525950-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.9 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592557
CATALOG NUMBER: HCC4W05D010BZ-HM40525950-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P592557

CATALOG NUMBER: HCC4W05D010BZ-HM40525950-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50781
5°	50505
10°	49586
15°	48538
20°	46467
25°	43211
30°	38242
35°	30176
40°	22591
45°	17356
50°	14085
55°	11699
60°	10336
65°	9573
70°	8836
75°	8102
80°	7316
85°	5944



TEST NUMBER: P592557
 CATALOG NUMBER: HCC4W05D010BZ-HM40525950-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	6.4
10°-20°	106.6	17.8
20°-30°	144.7	24.2
30°-40°	125.4	20.9
40°-50°	78.7	13.1
50°-60°	49.5	8.3
60°-70°	32.5	5.4
70°-80°	17.9	3.0
80°-90°	4.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.9	48.4
0°-40°	415.3	69.3
0°-60°	543.5	90.8
0°-90°	598.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	412	
5°	408	39
15°	380	107
25°	318	145
35°	200	125
45°	100	79
55°	54	50
65°	33	33
75°	17	18
85°	4	5
90°	0	



TEST NUMBER: P592557
CATALOG NUMBER: HCC4W05D010BZ-HM40525950-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	411.7
2.5°	409.2
5°	407.9
7.5°	403.7
10°	395.9
12.5°	387.9
15°	380.1
17.5°	369.3
20°	354.0
22.5°	336.5
25°	317.5
27.5°	295.4
30°	268.5
32.5°	235.7
35°	200.4
37.5°	168.1
40°	140.3
42.5°	118.3
45°	99.5
47.5°	85.5
50°	73.4
52.5°	63.1
55°	54.4
57.5°	46.9
60°	41.9
62.5°	37.3
65°	32.8
67.5°	28.3
70°	24.5
72.5°	20.3
75°	17.0
77.5°	13.3
80°	10.3
82.5°	7.0
85°	4.2
87.5°	1.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)