

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581415

Luminaire Tested: **HCC4W07D010BZ-HM40525827-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581415  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010BZ-HM40525827-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 896.0 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581415  
CATALOG NUMBER: HCC4W07D010BZ-HM40525827-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581415  
 CATALOG NUMBER: HCC4W07D010BZ-HM40525827-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91	88	86	85
3	101	93	88	84	98	92	87	83	89	85	82		87	83	80		85	82	79	77
4	95	86	80	76	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74	70	66	65
6	84	74	67	63	82	73	67	62	72	66	62		70	65	62		69	65	61	60
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64	60	56	55
8	75	64	57	53	73	63	57	53	62	57	53		61	56	52		60	56	52	51
9	70	60	53	49	69	59	53	49	58	53	49		57	52	48		56	52	48	47
10	67	56	50	45	66	55	49	45	55	49	45		54	49	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72379
5°	73436
10°	75738
15°	80934
20°	85753
25°	84829
30°	76127
35°	59252
40°	40141
45°	25049
50°	10861
55°	3656
60°	888
65°	642
70°	361
75°	286
80°	426
85°	0



TEST NUMBER: P581415  
 CATALOG NUMBER: HCC4W07D010BZ-HM40525827-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.0	6.4
10°-20°	179.9	20.1
20°-30°	281.9	31.5
30°-40°	243.3	27.2
40°-50°	111.9	12.5
50°-60°	19.0	2.1
60°-70°	2.1	0.2
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.8	57.9
0°-40°	762.1	85.1
0°-60°	892.9	99.7
0°-90°	896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	587	
5°	593	57
15°	634	180
25°	623	282
35°	394	243
45°	144	112
55°	17	19
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581415  
CATALOG NUMBER: HCC4W07D010BZ-HM40525827-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	586.8
2.5°	586.8
5°	593.1
7.5°	598.9
10°	604.7
12.5°	616.9
15°	633.8
17.5°	648.1
20°	653.3
22.5°	645.4
25°	623.3
27.5°	587.3
30°	534.5
32.5°	467.9
35°	393.5
37.5°	318.5
40°	249.3
42.5°	190.6
45°	143.6
47.5°	100.8
50°	56.6
52.5°	31.2
55°	17.0
57.5°	8.4
60°	3.6
62.5°	2.6
65°	2.2
67.5°	1.6
70°	1.0
72.5°	1.0
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)