

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581408

Luminaire Tested: **HCC4S07D010MB-HM40525827-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MB-HM40525827-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.3 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581408
CATALOG NUMBER: HCC4S07D010MB-HM40525827-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P581408

CATALOG NUMBER: HCC4S07D010MB-HM40525827-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59				
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54				
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49				
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69962
5°	70278
10°	70765
15°	71485
20°	70278
25°	67041
30°	60930
35°	49148
40°	34103
45°	22398
50°	15006
55°	10666
60°	9128
65°	10507
70°	11252
75°	10866
80°	9802
85°	9057



TEST NUMBER: P581408
 CATALOG NUMBER: HCC4S07D010MB-HM40525827-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	6.3
10°-20°	157.2	18.5
20°-30°	224.7	26.4
30°-40°	200.7	23.6
40°-50°	103.0	12.1
50°-60°	46.8	5.5
60°-70°	34.9	4.1
70°-80°	23.8	2.8
80°-90°	7.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	436.0	51.2
0°-40°	636.7	74.7
0°-60°	786.5	92.3
0°-90°	852.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	567	
5°	568	54
15°	560	157
25°	493	225
35°	326	201
45°	128	103
55°	50	47
65°	36	35
75°	23	24
85°	6	7
90°	0	



TEST NUMBER: P581408
CATALOG NUMBER: HCC4S07D010MB-HM40525827-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	567.2
2.5°	565.0
5°	567.6
7.5°	567.6
10°	565.0
12.5°	562.4
15°	559.8
17.5°	551.8
20°	535.4
22.5°	515.4
25°	492.6
27.5°	464.2
30°	427.8
32.5°	381.2
35°	326.4
37.5°	267.8
40°	211.8
42.5°	165.2
45°	128.4
47.5°	100.4
50°	78.2
52.5°	61.2
55°	49.6
57.5°	41.8
60°	37.0
62.5°	36.0
65°	36.0
67.5°	34.8
70°	31.2
72.5°	27.0
75°	22.8
77.5°	18.0
80°	13.8
82.5°	10.0
85°	6.4
87.5°	2.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)