

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581453

Luminaire Tested: **HCC4W07D010SL-HM40525835-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581453  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010SL-HM40525835-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 815.6 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581453  
CATALOG NUMBER: HCC4W07D010SL-HM40525835-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581453

CATALOG NUMBER: HCC4W07D010SL-HM40525835-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	71651
5°	71133
10°	69275
15°	67437
20°	64423
25°	60019
30°	52855
35°	41695
40°	30255
45°	22241
50°	18076
55°	15182
60°	13765
65°	12608
70°	11721
75°	10723
80°	9731
85°	8350



TEST NUMBER: P581453  
 CATALOG NUMBER: HCC4W07D010SL-HM40525835-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.2	6.6
10°-20°	148.1	18.2
20°-30°	200.8	24.6
30°-40°	172.3	21.1
40°-50°	101.7	12.5
50°-60°	64.5	7.9
60°-70°	43.3	5.3
70°-80°	23.9	2.9
80°-90°	6.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.1	49.4
0°-40°	575.5	70.6
0°-60°	741.7	90.9
0°-90°	815.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	581	
5°	574	54
15°	528	148
25°	441	201
35°	277	172
45°	128	102
55°	71	65
65°	43	43
75°	22	24
85°	6	7
90°	0	



TEST NUMBER: P581453  
CATALOG NUMBER: HCC4W07D010SL-HM40525835-41NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	580.9
2.5°	576.7
5°	574.5
7.5°	566.7
10°	553.1
12.5°	541.2
15°	528.1
17.5°	511.5
20°	490.8
22.5°	467.7
25°	441.0
27.5°	409.6
30°	371.1
32.5°	325.5
35°	276.9
37.5°	230.0
40°	187.9
42.5°	152.9
45°	127.5
47.5°	109.0
50°	94.2
52.5°	81.8
55°	70.6
57.5°	61.7
60°	55.8
62.5°	49.8
65°	43.2
67.5°	37.9
70°	32.5
72.5°	27.3
75°	22.5
77.5°	17.8
80°	13.7
82.5°	9.4
85°	5.9
87.5°	2.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)