

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581461

Luminaire Tested: **HCC4S07D010MW-HM40525840-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MW-HM40525840-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 790.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581461
CATALOG NUMBER: HCC4S07D010MW-HM40525840-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581461
 CATALOG NUMBER: HCC4S07D010MW-HM40525840-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78793
5°	78859
10°	79007
15°	80168
20°	78166
25°	73329
30°	64861
35°	49329
40°	31076
45°	17845
50°	9460
55°	3935
60°	1036
65°	905
70°	649
75°	620
80°	426
85°	849



TEST NUMBER: P581461
 CATALOG NUMBER: HCC4S07D010MW-HM40525840-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	7.7
10°-20°	175.8	22.3
20°-30°	245.3	31.1
30°-40°	201.9	25.6
40°-50°	83.2	10.5
50°-60°	18.7	2.4
60°-70°	3.0	0.4
70°-80°	1.2	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.7	61.0
0°-40°	683.5	86.5
0°-60°	785.4	99.4
0°-90°	790.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	639	
5°	637	61
15°	628	176
25°	539	245
35°	328	202
45°	102	83
55°	18	19
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P581461
CATALOG NUMBER: HCC4S07D010MW-HM40525840-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	638.8
2.5°	635.7
5°	636.9
7.5°	634.4
10°	630.8
12.5°	629.0
15°	627.8
17.5°	616.8
20°	595.5
22.5°	568.8
25°	538.8
27.5°	503.0
30°	455.4
32.5°	397.0
35°	327.6
37.5°	257.5
40°	193.0
42.5°	140.7
45°	102.3
47.5°	73.1
50°	49.3
52.5°	31.1
55°	18.3
57.5°	9.1
60°	4.2
62.5°	3.6
65°	3.1
67.5°	2.4
70°	1.8
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)