

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592574

Luminaire Tested: **HCC4W07D010BZ-HM40525850-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592574  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010BZ-HM40525850-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1033.7 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592574  
CATALOG NUMBER: HCC4W07D010BZ-HM40525850-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P592574

CATALOG NUMBER: HCC4W07D010BZ-HM40525850-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91	88	86	85
3	101	93	88	84	98	92	87	83	89	85	82		87	83	80		85	82	79	77
4	95	86	80	76	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74	70	66	65
6	84	74	67	63	82	73	67	62	72	66	62		70	65	62		69	65	61	60
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64	60	56	55
8	75	64	57	53	73	63	57	53	62	57	53		61	56	52		60	56	52	51
9	70	60	53	49	69	59	53	49	58	53	49		57	52	48		56	52	48	47
10	67	56	50	45	66	55	49	45	55	49	45		54	49	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	83505
5°	84728
10°	87386
15°	93372
20°	98932
25°	97854
30°	87835
35°	68347
40°	46308
45°	28904
50°	12511
55°	4193
60°	1036
65°	700
70°	469
75°	286
80°	426
85°	0



TEST NUMBER: P592574  
 CATALOG NUMBER: HCC4W07D010BZ-HM40525850-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.7	6.4
10°-20°	207.6	20.1
20°-30°	325.2	31.5
30°-40°	280.7	27.2
40°-50°	129.1	12.5
50°-60°	21.9	2.1
60°-70°	2.5	0.2
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.5	57.9
0°-40°	879.2	85.1
0°-60°	1030.2	99.7
0°-90°	1033.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	677	
5°	684	66
15°	731	208
25°	719	325
35°	454	281
45°	166	129
55°	20	22
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P592574  
CATALOG NUMBER: HCC4W07D010BZ-HM40525850-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	677.0
2.5°	677.0
5°	684.3
7.5°	691.0
10°	697.7
12.5°	711.7
15°	731.2
17.5°	747.7
20°	753.7
22.5°	744.6
25°	719.0
27.5°	677.6
30°	616.7
32.5°	539.9
35°	453.9
37.5°	367.5
40°	287.6
42.5°	220.0
45°	165.7
47.5°	116.4
50°	65.2
52.5°	36.0
55°	19.5
57.5°	9.8
60°	4.2
62.5°	3.1
65°	2.4
67.5°	1.8
70°	1.3
72.5°	1.3
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)