

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581515

Luminaire Tested: **HCC4S07D010MB-HM40525935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MB-HM40525935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 686.7 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581515
CATALOG NUMBER: HCC4S07D010MB-HM40525935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581515

CATALOG NUMBER: HCC4S07D010MB-HM40525935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93					93			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85					85			
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72					72			
5	90	81	74	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66					66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61					61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56					56			
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52					52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49					49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45					45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68469
5°	68533
10°	68674
15°	69671
20°	67941
25°	63734
30°	56373
35°	42869
40°	27002
45°	15507
50°	8232
55°	3419
60°	937
65°	759
70°	577
75°	477
80°	426
85°	849



TEST NUMBER: P581515
 CATALOG NUMBER: HCC4S07D010MB-HM40525935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	7.7
10°-20°	152.8	22.2
20°-30°	213.2	31.0
30°-40°	175.4	25.5
40°-50°	72.3	10.5
50°-60°	16.3	2.4
60°-70°	2.6	0.4
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.6	61.0
0°-40°	594.1	86.5
0°-60°	682.6	99.4
0°-90°	686.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	555	
5°	554	53
15°	546	153
25°	468	213
35°	285	175
45°	89	72
55°	16	16
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P581515
CATALOG NUMBER: HCC4S07D010MB-HM40525935-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	555.1
2.5°	552.5
5°	553.5
7.5°	551.4
10°	548.3
12.5°	546.7
15°	545.6
17.5°	536.1
20°	517.6
22.5°	494.2
25°	468.3
27.5°	437.1
30°	395.8
32.5°	345.0
35°	284.7
37.5°	223.8
40°	167.7
42.5°	122.2
45°	88.9
47.5°	63.5
50°	42.9
52.5°	27.0
55°	15.9
57.5°	8.0
60°	3.8
62.5°	3.2
65°	2.6
67.5°	2.2
70°	1.6
72.5°	1.0
75°	1.0
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)