

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581519

Luminaire Tested: **HCC4W07D010MB-HM40525935-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MB-HM40525935-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.5 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581519
CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581519

CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84				84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63				63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	68	63	60	58				58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53				53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49				49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45				45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42				42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71084
5°	71603
10°	72506
15°	74332
20°	74872
25°	72730
30°	66684
35°	54870
40°	39996
45°	25974
50°	14622
55°	6946
60°	2763
65°	1693
70°	1154
75°	763
80°	426
85°	849



TEST NUMBER: P581519
 CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	6.5
10°-20°	164.1	19.4
20°-30°	243.4	28.8
30°-40°	224.8	26.6
40°-50°	117.4	13.9
50°-60°	32.2	3.8
60°-70°	6.2	0.7
70°-80°	1.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.7	54.7
0°-40°	687.5	81.3
0°-60°	837.1	99.0
0°-90°	845.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	578	55
15°	582	164
25°	534	243
35°	364	225
45°	149	117
55°	32	32
65°	6	6
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581519
CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	576.3
2.5°	574.7
5°	578.3
7.5°	579.9
10°	578.9
12.5°	579.9
15°	582.1
17.5°	579.9
20°	570.4
22.5°	555.0
25°	534.4
27.5°	506.3
30°	468.2
32.5°	420.0
35°	364.4
37.5°	306.1
40°	248.4
42.5°	195.4
45°	148.9
47.5°	109.1
50°	76.2
52.5°	50.9
55°	32.3
57.5°	19.1
60°	11.2
62.5°	8.0
65°	5.8
67.5°	4.2
70°	3.2
72.5°	2.2
75°	1.6
77.5°	1.0
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)