

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581529

Luminaire Tested: **HCC4S07D010MB-HM40525935-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MB-HM40525935-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 812.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581529
CATALOG NUMBER: HCC4S07D010MB-HM40525935-41RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P581529

CATALOG NUMBER: HCC4S07D010MB-HM40525935-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52558	52558	52558
5°	53922	52560	51570
10°	55147	52091	50049
15°	56697	51360	48729
20°	56548	49394	46755
25°	54167	46246	44517
30°	49821	42600	42144
35°	43833	38653	38969
40°	37919	34602	36035
45°	32951	30753	32602
50°	29244	27114	28937
55°	25935	23784	24816
60°	23115	20623	20623
65°	20547	17132	16082
70°	17779	12983	11468
75°	14869	8578	7053
80°	11294	4120	3765
85°	5944	1415	1415



TEST NUMBER: P581529
 CATALOG NUMBER: HCC4S07D010MB-HM40525935-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.3	5.0
10°-20°	114.4	14.1
20°-30°	161.3	19.9
30°-40°	166.6	20.5
40°-50°	141.3	17.4
50°-60°	102.8	12.7
60°-70°	60.1	7.4
70°-80°	22.3	2.7
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.0	38.9
0°-40°	482.7	59.4
0°-60°	726.7	89.5
0°-90°	812.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	812.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	426	426	426	426	426	
5°	436	432	424	418	416	42
15°	444	430	402	385	382	125
25°	398	376	340	328	327	182
35°	291	278	257	257	259	182
45°	189	184	176	182	187	147
55°	121	115	111	114	115	109
65°	70	64	59	55	55	70
75°	31	26	18	14	15	34
85°	4	3	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581529

CATALOG NUMBER: HCC4S07D010MB-HM40525935-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	426.1	426.1	426.1	426.1	426.1	426.1	426.1	426.1	426.1
2.5°	429.7	428.7	427.7	426.1	423.9	422.3	420.7	419.7	419.7
5°	435.5	433.9	431.9	428.1	424.5	421.3	418.1	416.5	416.5
7.5°	439.8	437.7	433.5	428.1	421.7	417.1	412.3	410.1	409.1
10°	440.3	438.2	432.4	424.5	415.9	408.5	403.3	400.1	399.6
12.5°	441.4	438.7	431.3	420.3	409.1	400.1	394.3	391.1	390.0
15°	444.0	440.3	430.3	415.9	402.2	391.6	385.3	382.6	381.6
17.5°	441.4	436.1	423.9	406.9	391.6	380.0	373.6	371.0	371.0
20°	430.8	425.5	411.2	392.7	376.3	365.2	358.8	357.2	356.2
22.5°	415.9	410.1	394.8	375.2	358.8	348.8	344.6	342.4	341.9
25°	398.0	392.2	375.8	355.6	339.8	331.3	327.6	327.6	327.1
27.5°	377.8	370.4	353.6	336.1	320.7	314.3	312.7	312.7	313.3
30°	349.8	344.6	330.2	313.3	299.1	294.7	294.7	295.9	295.9
32.5°	319.7	315.9	303.3	288.5	277.3	274.7	275.7	277.9	278.4
35°	291.1	286.9	278.4	265.2	256.7	255.6	257.2	258.8	258.8
37.5°	263.0	258.8	253.0	242.4	236.0	236.6	238.6	240.8	242.4
40°	235.5	232.4	228.1	219.6	214.9	217.0	219.6	221.8	223.8
42.5°	211.2	208.0	204.8	198.5	195.3	197.9	201.1	203.2	205.3
45°	188.9	186.9	183.7	178.3	176.3	178.9	182.5	184.7	186.9
47.5°	169.9	168.9	164.6	159.8	158.8	161.4	164.6	167.3	168.9
50°	152.4	150.8	147.1	142.4	141.3	145.6	147.7	149.2	150.8
52.5°	135.5	133.9	129.6	125.4	125.4	128.6	130.2	130.8	132.3
55°	120.6	119.0	114.8	111.6	110.6	113.2	114.4	114.4	115.4
57.5°	106.9	105.3	101.1	97.4	96.8	98.4	98.4	98.4	99.0
60°	93.7	92.1	87.9	84.7	83.6	84.1	83.6	83.1	83.6
62.5°	81.5	79.9	75.7	71.9	70.9	70.9	69.3	68.8	69.3
65°	70.4	67.7	64.5	60.9	58.7	57.1	55.1	55.1	55.1
67.5°	59.3	57.1	53.5	49.7	47.1	44.5	41.3	42.3	42.9
70°	49.3	47.7	43.4	39.7	36.0	32.8	30.2	31.2	31.8
72.5°	40.2	38.1	34.4	30.2	27.0	22.8	21.2	22.2	22.2
75°	31.2	29.1	25.9	21.7	18.0	14.3	14.3	14.8	14.8
77.5°	23.3	21.2	18.0	14.3	11.2	8.4	9.0	9.0	9.0
80°	15.9	14.3	11.6	8.4	5.8	4.8	4.8	4.8	5.3
82.5°	9.0	8.0	6.4	4.2	2.6	2.6	2.6	2.6	2.6
85°	4.2	3.2	2.6	1.6	1.0	1.0	1.0	1.0	1.0
87.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)