

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581575

Luminaire Tested: **HCC6W10D010MB-HM60525830-61PSMDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W10D010MB-HM60525830-61PSMDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1105.2 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581575  
CATALOG NUMBER: HCC6W10D010MB-HM60525830-61PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581575  
 CATALOG NUMBER: HCC6W10D010MB-HM60525830-61PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39498
5°	39390
10°	38805
15°	38190
20°	36934
25°	35173
30°	32119
35°	25859
40°	17433
45°	12707
50°	10985
55°	9921
60°	9418
65°	8911
70°	8383
75°	7943
80°	7387
85°	6919



TEST NUMBER: P581575  
 CATALOG NUMBER: HCC6W10D010MB-HM60525830-61PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.7	6.1
10°-20°	189.0	17.1
20°-30°	265.5	24.0
30°-40°	236.3	21.4
40°-50°	132.1	12.0
50°-60°	94.1	8.5
60°-70°	68.5	6.2
70°-80°	39.7	3.6
80°-90°	12.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.2	47.3
0°-40°	758.5	68.6
0°-60°	984.7	89.1
0°-90°	1105.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1105.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	720	
5°	716	68
15°	673	189
25°	582	265
35°	386	236
45°	164	132
55°	104	94
65°	69	68
75°	38	40
85°	11	12
90°	0	



TEST NUMBER: P581575  
CATALOG NUMBER: HCC6W10D010MB-HM60525830-61PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	720.5
2.5°	717.3
5°	715.8
7.5°	709.5
10°	697.1
12.5°	685.4
15°	672.9
17.5°	655.8
20°	633.1
22.5°	608.1
25°	581.5
27.5°	548.8
30°	507.4
32.5°	454.3
35°	386.4
37.5°	309.9
40°	243.6
42.5°	194.4
45°	163.9
47.5°	143.7
50°	128.8
52.5°	115.6
55°	103.8
57.5°	94.4
60°	85.9
62.5°	78.1
65°	68.7
67.5°	60.9
70°	52.3
72.5°	44.5
75°	37.5
77.5°	30.5
80°	23.4
82.5°	17.2
85°	11.0
87.5°	5.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)