

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581582

Luminaire Tested: **HCC6W10D010MB-HM60525830-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581582  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W10D010MB-HM60525830-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1227.7 lumens  
Efficiency: N/A  
Efficacy: 124.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581582  
CATALOG NUMBER: HCC6W10D010MB-HM60525830-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P581582

CATALOG NUMBER: HCC6W10D010MB-HM60525830-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	82
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77	75
4	93	85	78	73	91	83	78	73	81	76	72		79	75	71		77	73	70	69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60		69	64	60		67	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	48	45		53	48	44		53	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	45786
5°	46181
10°	47839
15°	51964
20°	54051
25°	51699
30°	44621
35°	32130
40°	18098
45°	9381
50°	5586
55°	4024
60°	3421
65°	3956
70°	5001
75°	5295
80°	5177
85°	4906



TEST NUMBER: P581582  
 CATALOG NUMBER: HCC6W10D010MB-HM60525830-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	6.6
10°-20°	258.2	21.0
20°-30°	386.0	31.4
30°-40°	295.1	24.0
40°-50°	103.1	8.4
50°-60°	39.2	3.2
60°-70°	30.8	2.5
70°-80°	26.1	2.1
80°-90°	8.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.0	59.1
0°-40°	1020.0	83.1
0°-60°	1162.3	94.7
0°-90°	1227.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	835	
5°	839	81
15°	916	258
25°	855	386
35°	480	295
45°	121	103
55°	42	39
65°	30	31
75°	25	26
85°	8	8
90°	0	



TEST NUMBER: P581582  
CATALOG NUMBER: HCC6W10D010MB-HM60525830-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	835.2
2.5°	832.8
5°	839.2
7.5°	847.6
10°	859.4
12.5°	885.9
15°	915.6
17.5°	933.6
20°	926.5
22.5°	898.5
25°	854.7
27.5°	792.3
30°	704.9
32.5°	600.3
35°	480.1
37.5°	355.9
40°	252.9
42.5°	177.2
45°	121.0
47.5°	85.1
50°	65.5
52.5°	51.5
55°	42.1
57.5°	34.3
60°	31.2
62.5°	30.5
65°	30.5
67.5°	32.0
70°	31.2
72.5°	28.9
75°	25.0
77.5°	21.1
80°	16.4
82.5°	11.7
85°	7.8
87.5°	3.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)