

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581588

Luminaire Tested: **HCC6W10D010MB-HM60525835-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W10D010MB-HM60525835-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1250.5 lumens  
Efficiency: N/A  
Efficacy: 126.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581588  
CATALOG NUMBER: HCC6W10D010MB-HM60525835-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581588  
 CATALOG NUMBER: HCC6W10D010MB-HM60525835-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	59381
5°	60307
10°	63743
15°	70971
20°	73600
25°	60391
30°	42310
35°	28871
40°	15035
45°	5280
50°	2362
55°	755
60°	439
65°	311
70°	256
75°	169
80°	0
85°	0



TEST NUMBER: P581588  
 CATALOG NUMBER: HCC6W10D010MB-HM60525835-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.2	8.5
10°-20°	351.7	28.1
20°-30°	447.8	35.8
30°-40°	266.9	21.3
40°-50°	64.7	5.2
50°-60°	9.9	0.8
60°-70°	2.5	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	905.7	72.4
0°-40°	1172.6	93.8
0°-60°	1247.2	99.7
0°-90°	1250.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1250.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1083	
5°	1096	106
15°	1250	352
25°	998	448
35°	431	267
45°	68	65
55°	8	10
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581588  
CATALOG NUMBER: HCC6W10D010MB-HM60525835-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1083.2
2.5°	1083.2
5°	1095.9
7.5°	1115.7
10°	1145.1
12.5°	1191.1
15°	1250.5
17.5°	1287.9
20°	1261.6
22.5°	1161.0
25°	998.4
27.5°	819.1
30°	668.4
32.5°	546.4
35°	431.4
37.5°	318.0
40°	210.1
42.5°	113.4
45°	68.1
47.5°	42.8
50°	27.7
52.5°	16.6
55°	7.9
57.5°	4.8
60°	4.0
62.5°	3.2
65°	2.4
67.5°	1.6
70°	1.6
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)