

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581600

Luminaire Tested: **HCC6W10D010MB-HM60525835-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581600  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W10D010MB-HM60525835-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1157.6 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581600  
CATALOG NUMBER: HCC6W10D010MB-HM60525835-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581600

CATALOG NUMBER: HCC6W10D010MB-HM60525835-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39503
5°	39484
10°	39100
15°	38695
20°	37605
25°	36014
30°	33423
35°	28757
40°	20989
45°	14381
50°	11565
55°	10074
60°	9298
65°	8834
70°	8255
75°	7731
80°	7008
85°	5975



TEST NUMBER: P581600  
 CATALOG NUMBER: HCC6W10D010MB-HM60525835-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.0	5.9
10°-20°	191.5	16.5
20°-30°	272.3	23.5
30°-40°	262.2	22.6
40°-50°	150.9	13.0
50°-60°	95.6	8.3
60°-70°	67.6	5.8
70°-80°	38.6	3.3
80°-90°	11.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.8	45.9
0°-40°	794.0	68.6
0°-60°	1040.5	89.9
0°-90°	1157.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1157.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	721	
5°	718	68
15°	682	191
25°	595	272
35°	430	262
45°	186	151
55°	105	96
65°	68	68
75°	36	39
85°	10	11
90°	0	



TEST NUMBER: P581600  
CATALOG NUMBER: HCC6W10D010MB-HM60525835-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	720.6
2.5°	717.5
5°	717.5
7.5°	712.7
10°	702.4
12.5°	692.1
15°	681.8
17.5°	666.0
20°	644.6
22.5°	620.8
25°	595.4
27.5°	564.5
30°	528.0
32.5°	483.6
35°	429.7
37.5°	363.9
40°	293.3
42.5°	231.5
45°	185.5
47.5°	156.2
50°	135.6
52.5°	119.0
55°	105.4
57.5°	93.5
60°	84.8
62.5°	76.9
65°	68.1
67.5°	60.2
70°	51.5
72.5°	43.6
75°	36.5
77.5°	29.3
80°	22.2
82.5°	15.8
85°	9.5
87.5°	4.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)