

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581594

Luminaire Tested: **HCC6W10D010SL-HM60525835-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010SL-HM60525835-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1122.8 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581594
CATALOG NUMBER: HCC6W10D010SL-HM60525835-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581594
 CATALOG NUMBER: HCC6W10D010SL-HM60525835-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40134
5°	40023
10°	39428
15°	38803
20°	37523
25°	35742
30°	32632
35°	26274
40°	17712
45°	12908
50°	11164
55°	10083
60°	9572
65°	9054
70°	8511
75°	8049
80°	7514
85°	6982



TEST NUMBER: P581594
 CATALOG NUMBER: HCC6W10D010SL-HM60525835-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	6.1
10°-20°	192.0	17.1
20°-30°	269.7	24.0
30°-40°	240.1	21.4
40°-50°	134.2	11.9
50°-60°	95.6	8.5
60°-70°	69.6	6.2
70°-80°	40.2	3.6
80°-90°	12.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.6	47.3
0°-40°	770.7	68.6
0°-60°	1000.5	89.1
0°-90°	1122.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1122.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	732	
5°	727	69
15°	684	192
25°	591	270
35°	393	240
45°	166	134
55°	106	96
65°	70	70
75°	38	40
85°	11	12
90°	0	



TEST NUMBER: P581594
CATALOG NUMBER: HCC6W10D010SL-HM60525835-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	732.1
2.5°	728.9
5°	727.3
7.5°	721.0
10°	708.3
12.5°	696.4
15°	683.7
17.5°	666.3
20°	643.2
22.5°	617.8
25°	590.9
27.5°	557.6
30°	515.5
32.5°	461.6
35°	392.6
37.5°	314.9
40°	247.5
42.5°	197.5
45°	166.5
47.5°	145.9
50°	130.9
52.5°	117.4
55°	105.5
57.5°	96.0
60°	87.3
62.5°	79.4
65°	69.8
67.5°	61.9
70°	53.1
72.5°	45.2
75°	38.0
77.5°	30.9
80°	23.8
82.5°	17.4
85°	11.1
87.5°	5.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)