

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581606

Luminaire Tested: **HCC6S10D010SL-HM60525840-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581606  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S10D010SL-HM60525840-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1159.8 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581606  
CATALOG NUMBER: HCC6S10D010SL-HM60525840-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581606  
 CATALOG NUMBER: HCC6S10D010SL-HM60525840-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86	83	80	79
4	96	88	82	77	94	86	81	77	84	79	76		82	78	75		80	77	74	72
5	90	81	75	71	89	80	75	70	79	74	70		77	73	69		75	72	68	67
6	85	76	70	65	84	75	69	65	74	68	64		72	67	64		71	67	63	62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67	62	59	57
8	77	67	60	56	75	66	60	56	65	59	55		64	59	55		63	58	55	53
9	73	62	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	52	48	57	52	48		57	52	48		56	51	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58087
5°	58040
10°	57430
15°	56277
20°	53315
25°	48142
30°	40892
35°	30196
40°	17468
45°	9265
50°	5245
55°	2733
60°	1798
65°	1271
70°	930
75°	699
80°	505
85°	503



TEST NUMBER: P581606  
 CATALOG NUMBER: HCC6S10D010SL-HM60525840-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.9	8.6
10°-20°	277.4	23.9
20°-30°	362.0	31.2
30°-40°	276.6	23.9
40°-50°	100.2	8.6
50°-60°	29.1	2.5
60°-70°	10.4	0.9
70°-80°	3.6	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.3	63.7
0°-40°	1015.9	87.6
0°-60°	1145.2	98.7
0°-90°	1159.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1060	
5°	1055	100
15°	992	277
25°	796	362
35°	451	277
45°	120	100
55°	29	29
65°	10	10
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P581606  
CATALOG NUMBER: HCC6S10D010SL-HM60525840-61MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1059.6
2.5°	1054.7
5°	1054.7
7.5°	1047.3
10°	1031.7
12.5°	1013.7
15°	991.6
17.5°	958.9
20°	913.9
22.5°	858.2
25°	795.9
27.5°	725.5
30°	646.0
32.5°	556.8
35°	451.2
37.5°	340.6
40°	244.1
42.5°	168.7
45°	119.5
47.5°	86.0
50°	61.5
52.5°	43.4
55°	28.6
57.5°	20.5
60°	16.4
62.5°	13.1
65°	9.8
67.5°	8.2
70°	5.8
72.5°	4.1
75°	3.3
77.5°	2.5
80°	1.6
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)