

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581610

Luminaire Tested: **HCC6W10D010BZ-HM60525840-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010BZ-HM60525840-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1114.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581610
CATALOG NUMBER: HCC6W10D010BZ-HM60525840-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581610

CATALOG NUMBER: HCC6W10D010BZ-HM60525840-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79				79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70				70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63				63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57				57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41				41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42190
5°	41993
10°	41065
15°	40102
20°	38591
25°	36504
30°	33170
35°	26850
40°	18105
45°	12443
50°	10192
55°	8927
60°	8442
65°	7965
70°	7469
75°	7117
80°	6472
85°	5724



TEST NUMBER: P581610
 CATALOG NUMBER: HCC6W10D010BZ-HM60525840-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	6.5
10°-20°	198.4	17.8
20°-30°	275.7	24.7
30°-40°	245.5	22.0
40°-50°	130.3	11.7
50°-60°	85.2	7.6
60°-70°	61.1	5.5
70°-80°	35.4	3.2
80°-90°	10.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.2	49.0
0°-40°	791.6	71.1
0°-60°	1007.1	90.4
0°-90°	1114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1114.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	763	72
15°	707	198
25°	604	276
35°	401	245
45°	160	130
55°	93	85
65°	61	61
75°	34	35
85°	9	10
90°	0	



TEST NUMBER: P581610
CATALOG NUMBER: HCC6W10D010BZ-HM60525840-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	769.6
2.5°	765.6
5°	763.1
7.5°	754.1
10°	737.7
12.5°	723.0
15°	706.6
17.5°	686.1
20°	661.5
22.5°	633.7
25°	603.5
27.5°	568.3
30°	524.0
32.5°	470.8
35°	401.2
37.5°	324.2
40°	253.0
42.5°	196.5
45°	160.5
47.5°	136.7
50°	119.5
52.5°	105.6
55°	93.4
57.5°	84.3
60°	77.0
62.5°	69.6
65°	61.4
67.5°	54.0
70°	46.6
72.5°	40.1
75°	33.6
77.5°	27.1
80°	20.5
82.5°	14.7
85°	9.1
87.5°	4.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)