

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581625

Luminaire Tested: **HCC6S10D010MB-HM60525927-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010MB-HM60525927-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 846.3 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581625
CATALOG NUMBER: HCC6S10D010MB-HM60525927-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581625

CATALOG NUMBER: HCC6S10D010MB-HM60525927-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84		89	85	82		86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60		69	64	59		67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55		64	58	54		62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	50		58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42		52	46	42		51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31505
5°	31389
10°	30867
15°	30324
20°	29274
25°	27758
30°	25244
35°	20177
40°	13461
45°	9590
50°	7991
55°	6967
60°	6578
65°	6200
70°	5690
75°	5316
80°	4830
85°	4277



TEST NUMBER: P581625
 CATALOG NUMBER: HCC6S10D010MB-HM60525927-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	6.4
10°-20°	150.0	17.7
20°-30°	209.6	24.8
30°-40°	184.7	21.8
40°-50°	99.7	11.8
50°-60°	66.7	7.9
60°-70°	47.3	5.6
70°-80°	26.6	3.1
80°-90°	7.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.6	48.9
0°-40°	598.2	70.7
0°-60°	764.7	90.4
0°-90°	846.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	575	
5°	570	54
15°	534	150
25°	459	210
35°	302	185
45°	124	100
55°	73	67
65°	48	47
75°	25	27
85°	7	8
90°	0	



TEST NUMBER: P581625
CATALOG NUMBER: HCC6S10D010MB-HM60525927-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.7
2.5°	571.7
5°	570.4
7.5°	564.9
10°	554.5
12.5°	544.7
15°	534.3
17.5°	520.2
20°	501.8
22.5°	481.6
25°	458.9
27.5°	432.5
30°	398.8
32.5°	357.1
35°	301.5
37.5°	240.8
40°	188.1
42.5°	148.3
45°	123.7
47.5°	107.2
50°	93.7
52.5°	82.7
55°	72.9
57.5°	66.2
60°	60.0
62.5°	53.9
65°	47.8
67.5°	41.7
70°	35.5
72.5°	30.0
75°	25.1
77.5°	20.3
80°	15.3
82.5°	11.0
85°	6.8
87.5°	3.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)