

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581628

Luminaire Tested: **HCC6W10D010MB-HM60525927-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010MB-HM60525927-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 834.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581628
CATALOG NUMBER: HCC6W10D010MB-HM60525927-61NDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581628

CATALOG NUMBER: HCC6W10D010MB-HM60525927-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31593
5°	31438
10°	30744
15°	30029
20°	28901
25°	27328
30°	24839
35°	20104
40°	13554
45°	9311
50°	7633
55°	6671
60°	6315
65°	5967
70°	5610
75°	5316
80°	4830
85°	4277



TEST NUMBER: P581628
 CATALOG NUMBER: HCC6W10D010MB-HM60525927-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	6.5
10°-20°	148.6	17.8
20°-30°	206.4	24.7
30°-40°	183.8	22.0
40°-50°	97.5	11.7
50°-60°	63.8	7.6
60°-70°	45.7	5.5
70°-80°	26.5	3.2
80°-90°	7.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.9	49.0
0°-40°	592.7	71.1
0°-60°	754.0	90.4
0°-90°	834.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	571	54
15°	529	149
25°	452	206
35°	300	184
45°	120	98
55°	70	64
65°	46	46
75°	25	27
85°	7	8
90°	0	



TEST NUMBER: P581628
CATALOG NUMBER: HCC6W10D010MB-HM60525927-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	576.3
2.5°	573.2
5°	571.3
7.5°	564.6
10°	552.3
12.5°	541.3
15°	529.1
17.5°	513.7
20°	495.4
22.5°	474.5
25°	451.8
27.5°	425.4
30°	392.4
32.5°	352.5
35°	300.4
37.5°	242.8
40°	189.4
42.5°	147.2
45°	120.1
47.5°	102.3
50°	89.5
52.5°	79.1
55°	69.8
57.5°	63.2
60°	57.6
62.5°	52.1
65°	46.0
67.5°	40.4
70°	35.0
72.5°	30.0
75°	25.1
77.5°	20.3
80°	15.3
82.5°	11.0
85°	6.8
87.5°	3.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)