

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581677

Luminaire Tested: **HCC6S10D010SL-HM60525940-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010SL-HM60525940-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.5 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581677
CATALOG NUMBER: HCC6S10D010SL-HM60525940-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P581677
 CATALOG NUMBER: HCC6S10D010SL-HM60525940-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75				
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70				
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65				
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61				
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57				
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53406
5°	54232
10°	57325
15°	63826
20°	66191
25°	54306
30°	38056
35°	25959
40°	13518
45°	4760
50°	2124
55°	679
60°	384
65°	285
70°	240
75°	148
80°	0
85°	0



TEST NUMBER: P581677
 CATALOG NUMBER: HCC6S10D010SL-HM60525940-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	8.5
10°-20°	316.3	28.1
20°-30°	402.7	35.8
30°-40°	240.0	21.3
40°-50°	58.2	5.2
50°-60°	8.9	0.8
60°-70°	2.2	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.5	72.4
0°-40°	1054.5	93.8
0°-60°	1121.6	99.7
0°-90°	1124.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	974	
5°	986	95
15°	1125	316
25°	898	403
35°	388	240
45°	61	58
55°	7	9
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581677
CATALOG NUMBER: HCC6S10D010SL-HM60525940-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	974.2
2.5°	974.2
5°	985.5
7.5°	1003.4
10°	1029.8
12.5°	1071.1
15°	1124.6
17.5°	1158.1
20°	1134.6
22.5°	1044.0
25°	897.8
27.5°	736.7
30°	601.2
32.5°	491.4
35°	387.9
37.5°	285.9
40°	188.9
42.5°	102.0
45°	61.4
47.5°	38.5
50°	24.9
52.5°	14.9
55°	7.1
57.5°	4.3
60°	3.5
62.5°	2.8
65°	2.2
67.5°	1.5
70°	1.5
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)