

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581679

Luminaire Tested: **HCC6W10D010BZ-HM60525940-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010BZ-HM60525940-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 984.7 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581679
CATALOG NUMBER: HCC6W10D010BZ-HM60525940-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581679

CATALOG NUMBER: HCC6W10D010BZ-HM60525940-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36664
5°	36523
10°	35916
15°	35284
20°	34064
25°	32300
30°	29378
35°	23477
40°	15658
45°	11164
50°	9305
55°	8105
60°	7653
65°	7212
70°	6620
75°	6185
80°	5619
85°	4906



TEST NUMBER: P581679
 CATALOG NUMBER: HCC6W10D010BZ-HM60525940-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.8	6.4
10°-20°	174.6	17.7
20°-30°	243.9	24.8
30°-40°	214.9	21.8
40°-50°	116.1	11.8
50°-60°	77.6	7.9
60°-70°	55.0	5.6
70°-80°	30.9	3.1
80°-90°	9.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.3	48.9
0°-40°	696.1	70.7
0°-60°	889.8	90.4
0°-90°	984.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	669	
5°	664	63
15°	622	175
25°	534	244
35°	351	215
45°	144	116
55°	85	78
65°	56	55
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P581679
CATALOG NUMBER: HCC6W10D010BZ-HM60525940-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	668.8
2.5°	665.2
5°	663.7
7.5°	657.4
10°	645.2
12.5°	633.8
15°	621.7
17.5°	605.3
20°	583.9
22.5°	560.3
25°	534.0
27.5°	503.3
30°	464.1
32.5°	415.7
35°	350.8
37.5°	280.2
40°	218.8
42.5°	172.5
45°	144.0
47.5°	124.7
50°	109.1
52.5°	96.2
55°	84.8
57.5°	77.0
60°	69.8
62.5°	62.7
65°	55.6
67.5°	48.4
70°	41.3
72.5°	35.0
75°	29.2
77.5°	23.5
80°	17.8
82.5°	12.8
85°	7.8
87.5°	3.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)