

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593071

Luminaire Tested: **HCC6S10D010BZ-HM60525950-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593071  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S10D010BZ-HM60525950-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1121.7 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593071  
CATALOG NUMBER: HCC6S10D010BZ-HM60525950-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P593071

CATALOG NUMBER: HCC6S10D010BZ-HM60525950-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41839
5°	42191
10°	43714
15°	47486
20°	49389
25°	47241
30°	40766
35°	29352
40°	16531
45°	8575
50°	5109
55°	3680
60°	3125
65°	3606
70°	4568
75°	4850
80°	4704
85°	4466



TEST NUMBER: P593071  
 CATALOG NUMBER: HCC6S10D010BZ-HM60525950-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	6.6
10°-20°	236.0	21.0
20°-30°	352.7	31.4
30°-40°	269.6	24.0
40°-50°	94.2	8.4
50°-60°	35.9	3.2
60°-70°	28.1	2.5
70°-80°	23.8	2.1
80°-90°	7.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.4	59.1
0°-40°	932.0	83.1
0°-60°	1062.1	94.7
0°-90°	1121.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1121.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	763	
5°	767	74
15°	837	236
25°	781	353
35°	439	270
45°	111	94
55°	38	36
65°	28	28
75°	23	24
85°	7	8
90°	0	



TEST NUMBER: P593071  
CATALOG NUMBER: HCC6S10D010BZ-HM60525950-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	763.2
2.5°	761.0
5°	766.7
7.5°	774.5
10°	785.3
12.5°	809.5
15°	836.7
17.5°	853.1
20°	846.6
22.5°	820.9
25°	781.0
27.5°	723.9
30°	644.0
32.5°	548.5
35°	438.6
37.5°	325.2
40°	231.0
42.5°	161.9
45°	110.6
47.5°	77.8
50°	59.9
52.5°	47.1
55°	38.5
57.5°	31.4
60°	28.5
62.5°	27.8
65°	27.8
67.5°	29.2
70°	28.5
72.5°	26.4
75°	22.9
77.5°	19.2
80°	14.9
82.5°	10.8
85°	7.1
87.5°	2.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)