

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593081

Luminaire Tested: **HCC6W10D010BZ-HM60525950-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010BZ-HM60525950-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.7 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593081
CATALOG NUMBER: HCC6W10D010BZ-HM60525950-61PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593081

CATALOG NUMBER: HCC6W10D010BZ-HM60525950-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36094
5°	35995
10°	35459
15°	34892
20°	33749
25°	32143
30°	29353
35°	23631
40°	15930
45°	11614
50°	10038
55°	9070
60°	8596
65°	8133
70°	7662
75°	7244
80°	6756
85°	6290



TEST NUMBER: P593081
 CATALOG NUMBER: HCC6W10D010BZ-HM60525950-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	6.1
10°-20°	172.7	17.1
20°-30°	242.6	24.0
30°-40°	216.0	21.4
40°-50°	120.7	12.0
50°-60°	86.0	8.5
60°-70°	62.5	6.2
70°-80°	36.2	3.6
80°-90°	11.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.2	47.3
0°-40°	693.1	68.6
0°-60°	899.8	89.1
0°-90°	1009.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	658	
5°	654	62
15°	615	173
25°	531	243
35°	353	216
45°	150	121
55°	95	86
65°	63	63
75°	34	36
85°	10	11
90°	0	



TEST NUMBER: P593081
CATALOG NUMBER: HCC6W10D010BZ-HM60525950-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	658.4
2.5°	655.5
5°	654.1
7.5°	648.4
10°	637.0
12.5°	626.2
15°	614.8
17.5°	599.2
20°	578.5
22.5°	555.6
25°	531.4
27.5°	501.5
30°	463.7
32.5°	415.1
35°	353.1
37.5°	283.2
40°	222.6
42.5°	177.6
45°	149.8
47.5°	131.2
50°	117.7
52.5°	105.6
55°	94.9
57.5°	86.3
60°	78.4
62.5°	71.3
65°	62.7
67.5°	55.6
70°	47.8
72.5°	40.6
75°	34.2
77.5°	27.8
80°	21.4
82.5°	15.7
85°	10.0
87.5°	5.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)