

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581715

Luminaire Tested: **HCC6S15D010BZ-HM60525830-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581715  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010BZ-HM60525830-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1472.6 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581715  
CATALOG NUMBER: HCC6S15D010BZ-HM60525830-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581715  
 CATALOG NUMBER: HCC6S15D010BZ-HM60525830-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54815
5°	54622
10°	53706
15°	52759
20°	50941
25°	48299
30°	43937
35°	35101
40°	23422
45°	16692
50°	13910
55°	12129
60°	11446
65°	10792
70°	9922
75°	9256
80°	8429
85°	7359



TEST NUMBER: P581715  
 CATALOG NUMBER: HCC6S15D010BZ-HM60525830-61MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	6.4
10°-20°	261.0	17.7
20°-30°	364.8	24.8
30°-40°	321.3	21.8
40°-50°	173.6	11.8
50°-60°	116.1	7.9
60°-70°	82.3	5.6
70°-80°	46.3	3.1
80°-90°	13.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.6	48.9
0°-40°	1040.9	70.7
0°-60°	1330.6	90.4
0°-90°	1472.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1472.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1000	
5°	993	94
15°	930	261
25°	798	365
35°	524	321
45°	215	174
55°	127	116
65°	83	82
75°	44	46
85°	12	13
90°	0	



TEST NUMBER: P581715  
CATALOG NUMBER: HCC6S15D010BZ-HM60525830-61MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	999.9
2.5°	994.6
5°	992.6
7.5°	982.9
10°	964.8
12.5°	947.7
15°	929.6
17.5°	905.0
20°	873.2
22.5°	838.0
25°	798.5
27.5°	752.6
30°	694.1
32.5°	621.5
35°	524.5
37.5°	418.9
40°	327.3
42.5°	258.0
45°	215.3
47.5°	186.6
50°	163.1
52.5°	143.9
55°	126.9
57.5°	115.1
60°	104.4
62.5°	93.9
65°	83.2
67.5°	72.5
70°	61.9
72.5°	52.2
75°	43.7
77.5°	35.2
80°	26.7
82.5°	19.2
85°	11.7
87.5°	5.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)