

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581718

Luminaire Tested: **HCC6S15D010SL-HM60525830-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581718  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010SL-HM60525830-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1451.2 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581718  
CATALOG NUMBER: HCC6S15D010SL-HM60525830-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581718

CATALOG NUMBER: HCC6S15D010SL-HM60525830-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54968
5°	54705
10°	53500
15°	52248
20°	50282
25°	47549
30°	43216
35°	34981
40°	23587
45°	16211
50°	13279
55°	11622
60°	10986
65°	10377
70°	9745
75°	9256
80°	8429
85°	7359



TEST NUMBER: P581718  
 CATALOG NUMBER: HCC6S15D010SL-HM60525830-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	6.5
10°-20°	258.5	17.8
20°-30°	359.1	24.7
30°-40°	319.8	22.0
40°-50°	169.8	11.7
50°-60°	111.0	7.6
60°-70°	79.6	5.5
70°-80°	46.1	3.2
80°-90°	13.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.5	49.0
0°-40°	1031.3	71.1
0°-60°	1312.1	90.4
0°-90°	1451.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1451.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1003	
5°	994	94
15°	921	259
25°	786	359
35°	523	320
45°	209	170
55°	122	111
65°	80	80
75°	44	46
85°	12	13
90°	0	



TEST NUMBER: P581718  
CATALOG NUMBER: HCC6S15D010SL-HM60525830-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1002.7
2.5°	997.3
5°	994.1
7.5°	982.5
10°	961.1
12.5°	941.9
15°	920.6
17.5°	893.9
20°	861.9
22.5°	825.6
25°	786.1
27.5°	740.2
30°	682.7
32.5°	613.4
35°	522.7
37.5°	422.4
40°	329.6
42.5°	256.1
45°	209.1
47.5°	178.1
50°	155.7
52.5°	137.6
55°	121.6
57.5°	109.9
60°	100.2
62.5°	90.7
65°	80.0
67.5°	70.4
70°	60.8
72.5°	52.3
75°	43.7
77.5°	35.2
80°	26.7
82.5°	19.2
85°	11.7
87.5°	5.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)