

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581725

Luminaire Tested: **HCC6W15D010MB-HM60525830-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010MB-HM60525830-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1556.8 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581725
CATALOG NUMBER: HCC6W15D010MB-HM60525830-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P581725

CATALOG NUMBER: HCC6W15D010MB-HM60525830-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53126
5°	53098
10°	52576
15°	52038
20°	50568
25°	48426
30°	44950
35°	38668
40°	28224
45°	19343
50°	15547
55°	13553
60°	12510
65°	11895
70°	11108
75°	10379
80°	9439
85°	8051



TEST NUMBER: P581725
 CATALOG NUMBER: HCC6W15D010MB-HM60525830-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	5.9
10°-20°	257.5	16.5
20°-30°	366.2	23.5
30°-40°	352.6	22.6
40°-50°	202.9	13.0
50°-60°	128.5	8.3
60°-70°	91.0	5.8
70°-80°	51.9	3.3
80°-90°	14.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.2	45.9
0°-40°	1067.8	68.6
0°-60°	1399.1	89.9
0°-90°	1556.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1556.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	969	
5°	965	91
15°	917	257
25°	801	366
35°	578	353
45°	250	203
55°	142	129
65°	92	91
75°	49	52
85°	13	15
90°	0	



TEST NUMBER: P581725
CATALOG NUMBER: HCC6W15D010MB-HM60525830-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	969.1
2.5°	964.9
5°	964.9
7.5°	958.4
10°	944.5
12.5°	930.7
15°	916.9
17.5°	895.5
20°	866.8
22.5°	834.8
25°	800.6
27.5°	759.1
30°	710.1
32.5°	650.4
35°	577.8
37.5°	489.3
40°	394.4
42.5°	311.3
45°	249.5
47.5°	210.0
50°	182.3
52.5°	159.9
55°	141.8
57.5°	125.8
60°	114.1
62.5°	103.4
65°	91.7
67.5°	81.0
70°	69.3
72.5°	58.7
75°	49.0
77.5°	39.5
80°	29.9
82.5°	21.3
85°	12.8
87.5°	5.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)